

Military Cross Reference (Available P/N's)



The PANDUIT Cable Ties and Marker Ties listed in the following tables meet all of the testing requirements of Aerospace Standard SAE-AS23190A (formerly MIL-S-23190E) and the dimensional requirements of Aerospace Standards SAE-AS33671 (formerly MS3367) and SAE-AS33681 (formerly MS3368).

* Weather Resistant per ASTM D 4066-94B

Rev. 10-16-07

Cable Tie Cross Reference

Mil. Std. Part Number	Color	Pan-Ty®	Dome-Top® Barb Ty	Sta-Strap®	Belt-Ty™ In-Line	Contour-Ty®
MS3367-1-0	Black *	PLT2S-C00, -M00	---	---	---	---
MS3367-1-1	Brown	PLT2S-C1, -M1	BT2S-M1	---	---	---
MS3367-1-2	Red	PLT2S-C2, -M2	BT2S-M2	---	---	---
MS3367-1-3	Orange	PLT2S-C3, -M3	BT2S-M3	---	---	---
MS3367-1-4	Yellow	PLT2S-C4Y, -M4Y	BT2S-M4Y	---	---	---
MS3367-1-5	Green	PLT2S-C5, -M5	BT2S-M5	---	---	---
MS3367-1-6	Blue	PLT2S-C6, -M6	BT2S-M6	---	---	---
MS3367-1-7	Purple	PLT2S-C7, -M7	BT2S-M7	---	---	---
MS3367-1-8	Gray	PLT2S-C8, -M8	BT2S-M8	---	---	---
MS3367-1-9	Natural	PLT2S-C, -M, -VMR	BT2S-C, -M	SST2S-C, -M	---	---
MS3367-2-0	Black *	PLT4S-C00, -M00	---	---	---	---
MS3367-2-1	Brown	PLT4S-M1	---	---	---	---
MS3367-2-2	Red	PLT4S-C2, -M2	BT4S-M2	SST4S-M2	---	---
MS3367-2-3	Orange	PLT4S-C3, -M3	BT4S-M3	---	---	---
MS3367-2-4	Yellow	PLT4S-C4Y, -M4Y	BT4S-M4Y	---	---	---
MS3367-2-5	Green	PLT4S-C5, -M5	BT4S-M5	---	---	---
MS3367-2-6	Blue	PLT4S-C6, -M6	BT4S-M6	---	---	---
MS3367-2-7	Purple	PLT4S-C7, -M7	BT4S-M7	---	---	---
MS3367-2-8	Gray	PLT4S-C8, -M8	BT4S-M8	---	---	---
MS3367-2-9	Natural	PLT4S-C, -M	BT4S-C, -M	SST4S-C, -M	---	---
MS3367-3-0	Black *	PLT4H-L00, -TL00	---	---	---	---
MS3367-3-1	Brown	PLT4H-TL1	---	---	---	---
MS3367-3-2	Red	PLT4H-TL2	---	---	---	---
MS3367-3-3	Orange	PLT4H-TL3	---	---	---	---
MS3367-3-4	Yellow	PLT4H-TL4Y	---	---	---	---
MS3367-3-5	Green	PLT4H-TL5	---	---	---	---
MS3367-3-6	Blue	PLT4H-TL6	---	---	---	---
MS3367-3-9	Natural	PLT4H-L, -C, -TL	BT4LH-L, -TL	SST4H-L, -D	---	---
MS3367-4-0	Black *	PLT1M-C00, -M00, -XMR00	---	---	---	---
MS3367-4-0	Black *	PLT1.5M-XMR00	---	---	---	---
MS3367-4-1	Brown	PLT1M-C1, -M1, -XMR1	BT1M-M1	---	---	---
MS3367-4-2	Red	PLT1M-C2, -M2, -XMR2	BT1M-M2	---	---	---
MS3367-4-3	Orange	PLT1M-C3, -M3, -XMR3	BT1M-M3	---	---	---
MS3367-4-4	Yellow	PLT1M-C4Y, -M4Y, -XMR4Y	BT1M-M4Y	---	---	---
MS3367-4-5	Green	PLT1M-C5, -M5, -XMR5	BT1M-M5	---	---	---
MS3367-4-6	Blue	PLT1M-C6, -M6, -XMR6	BT1M-M6	---	---	---
MS3367-4-7	Purple	PLT1M-C7, -M7, -XMR7	BT1M-M7	---	---	---
MS3367-4-8	Gray	PLT1M-C8, -M8, -XMR8	BT1M-M8	---	---	---
MS3367-4-9	Natural	PLT1M-C, -M, -XMR	BT1M-C, -M, -XMR	SST1M-C, -M	---	---
MS3367-4-9	Natural	PLT.7M-C, -M	---	---	---	---
MS3367-4-9	Natural	PLT1.5M-XMR	BT1.5M-XMR	---	---	---
MS3367-5-0	Black *	PLT1.5I-M00	---	---	---	---
MS3367-5-1	Brown	PLT1.5I-C1, -M1	BT1.5I-M1	---	---	---
MS3367-5-2	Red	PLT1.5I-C2, -M2	BT1.5I-M2	---	---	---
MS3367-5-3	Orange	PLT1.5I-C3, -M3	BT1.5I-M3	---	---	---
MS3367-5-4	Yellow	PLT1.5I-C4Y, -M4Y	BT1.5I-M4Y	---	---	---
MS3367-5-5	Green	PLT1.5I-C5, -M5	BT1.5I-M5	---	---	---
MS3367-5-6	Blue	PLT1.5I-C6, -M6	BT1.5I-M6	---	---	---
MS3367-5-7	Purple	PLT1.5I-C7, -M7	BT1.5I-M7	---	---	---
MS3367-5-8	Gray	PLT1.5I-C8, -M8	BT1.5I-M8	---	---	---

		Cable Tie Cross Reference				
Mil. Std. Part Number	Color	Pan-Ty®	Dome-Top® Barb Ty	Sta-Strap®	Belt-Ty™ In-Line	Contour-Ty®
MS3367-5-9	Natural	PLT1.5I-C, -M	BT1.5I-C, -M	SST1.5I-C, -M	---	---
MS3367-6-9	Natural	PLT8LH-L, -C,	BT8LH-L, -C	SST8H-L, -D	---	---
MS3367-6-9	Natural	---	BT9LH-L, -C	---	---	---
MS3367-7-0	Black *	PLT3S-C00, -M00	---	---	---	---
MS3367-7-1	Brown	PLT3S-M1	---	---	---	---
MS3367-7-2	Red	PLT3S-C2, -M2	BT3S-C2	---	---	---
MS3367-7-3	Orange	PLT3S-M3	---	---	---	---
MS3367-7-4	Yellow	PLT3S-M4Y	---	---	---	---
MS3367-7-5	Green	PLT3S-M5	---	---	---	---
MS3367-7-6	Blue	PLT3S-M6	---	---	---	---
MS3367-7-7	Purple	PLT3S-M7	---	---	---	---
MS3367-7-8	Gray	PLT3S-M8	---	---	---	---
MS3367-7-9	Natural	PLT3S-C, -M	BT3S-C, -M	SST3S-C, -M	---	---
MS3367-8-9	Natural	PLT5H-L, -C	---	---	---	---
MS3367-9-9	Natural	PLT6H-L, -C	---	---	---	---
MS3367-11-9	Natural	PLT8H-L, -C	---	---	---	---
MS3367-14-9	Natural	PLT13H-Q, -C	---	---	---	---
MS3367-20-9	Natural	PLT5EH-Q, -C	---	---	---	---
MS3367-21-9	Natural	PLT6EH-Q, -C	---	---	---	---
MS3367-22-9	Natural	PLT8EH-C	---	---	---	---
MS3367-23-9	Natural	---	---	---	ILT2S-C, -M	---
MS3367-24-9	Natural	---	---	---	ILT4S-C, -M	---
MS3367-25-9	Natural	---	---	---	ILT4LH-TL	---
MS3367-26-9	Natural	---	---	---	--	---
MS3367-27-9	Natural	---	---	---	--	---
MS3367-29-9	Natural	---	---	---	ILT3S-C, -M	---
MS3367-30-9	Natural	---	---	---	---	CBR1M-M
MS3367-31-9	Natural	---	---	---	---	CBR1.5M-M
MS3367-32-1	Brown	---	---	---	---	CBR2M-M1
MS3367-32-2	Red	---	---	---	---	CBR2M-M2
MS3367-32-3	Orange	---	---	---	---	CBR2M-M3
MS3367-32-4	Yellow	---	---	---	---	CBR2M-M4Y
MS3367-32-5	Green	---	---	---	---	CBR2M-M5
MS3367-32-6	Blue	---	---	---	---	CBR2M-M6
MS3367-32-7	Purple	---	---	---	---	CBR2M-M7
MS3367-32-9	Natural	---	---	---	---	CBR2M-M
MS3367-33-9	Natural	---	---	---	---	CBR1.5I-M
MS3367-34-1	Brown	---	---	---	---	CBR3I-M1
MS3367-34-2	Red	---	---	---	---	CBR3I-M2
MS3367-34-3	Orange	---	---	---	---	CBR3I-M3
MS3367-34-4	Yellow	---	---	---	---	CBR3I-M4Y
MS3367-34-5	Green	---	---	---	---	CBR3I-M5
MS3367-34-6	Blue	---	---	---	---	CBR3I-M6
MS3367-34-7	Purple	---	---	---	---	CBR3I-M7
MS3367-34-8	Gray	---	---	---	---	CBR3I-M8
MS3367-34-9	Natural	---	---	---	---	CBR3I-M
MS3367-35-9	Natural	---	---	---	---	CBR4I-M
MS3367-36-9	Natural	---	---	---	---	CBR2S-M
MS3367-37-9	Natural	---	---	---	---	CBR3S-M
MS3367-38-9	Natural	---	---	---	---	CBR4S-M
MS3367-39-9	Natural	---	---	---	---	CBR2HS-D
MS3367-40-9	Natural	---	---	---	---	CBR4LH-TL
MS3367-41-9	Natural	---	---	---	---	CBR6LH-C
MS3368-1-2A	Red	PLM2S-D2	---	---	---	---
MS3368-1-3A	Orange	PLM2S-D3	---	---	---	---
MS3368-1-4A	Yellow	PLM2S-C4Y, -D4Y	---	---	---	---

		Cable Tie Cross Reference				
Mil. Std. Part Number	Color	Pan-Ty®	Dome-Top® Barb Ty	Sta-Strap®	Belt-Ty™ In-Line	Contour-Ty®
MS3368-1-5A	Green	PLM2S-D5	---	---	---	---
MS3368-1-6A	Blue	PLM2S-D6	---	---	---	---
MS3368-1-8A	Gray	PLM2S-D8	---	---	---	---
MS3368-1-9A	Natural	PLM2S-C, -D	BM2S-C, -D	---	---	---
MS3368-1-9B	Natural	---	---	SSM2S-C, -D	---	---
MS3368-2-2A	Red	PLM4S-D2	---	---	---	---
MS3368-2-4A	Yellow	PLM4S-D4Y	---	---	---	---
MS3368-2-6A	Blue	PLM4S-D6	---	---	---	---
MS3368-2-9A	Natural	PLM4S-C, -D	BM4S-C, -D	---	---	---
MS3368-2-9B	Natural	---	---	SSM4S-D	---	---
MS3368-3-4C	Yellow	PL2M2S-D4Y	---	---	---	---
MS3368-3-9C	Natural	PL2M2S-L, -D	B2M2S-D	---	---	---
MS3368-4-4D	Yellow	PL3M2S-D4Y	---	---	---	---
MS3368-4-9D	Natural	PL3M2S-L, -D	B3M2S-TL	---	---	---
MS3368-5-1E	Brown	PLM1M-M1	---	---	---	---
MS3368-5-2E	Red	PLM1M-M2	---	---	---	---
MS3368-5-3E	Orange	PLM1M-M3	---	---	---	---
MS3368-5-4E	Yellow	PLM1M-M4Y	---	---	---	---
MS3368-5-5E	Green	PLM1M-M5	---	---	---	---
MS3368-5-6E	Blue	PLM1M-M6	---	---	---	---
MS3368-5-7E	Purple	PLM1M-M7	---	---	---	---
MS3368-5-8E	Gray	PLM1M-M8	---	---	---	---
MS3368-5-9E	Natural	PLM1M-C, -M	BM1M-C, -M	---	---	---

Installation Tools

The *PANDUIT* Installation Tools listed in the table below meet all of the testing requirements of MIL-T-81306 and the dimensional requirements of MS90387.

Mil. Std. Part Number	<i>PANDUIT</i> P/N
MS90387-1	GTS, GS2B
MS90387-2	GS4H