


- [Contact Us](#)
- [Global Locations](#)
- [Product Support](#)



**Where To Buy**

Enter Zip Code:

Enter Quantity:

**Pin Terminals**

**T&B Catalog Number:** 14RB-47PT  
**UPC Number:** 78621003416  
**Status:** Active

**Description:**  
 Insulated Vinyl Pin Terminals For Wire Range 16-14 Length .87 Diameter .075

ROHS SUBMITTAL PACKAGE

**Features**

- Provides an easy and effective way to terminate stranded wire into European/metric-style terminal blocks.

**General**

|                 |                     |
|-----------------|---------------------|
| Insulation Type | Insulated Vinyl     |
| Terminal Series | RB                  |
| Material        | Copper              |
| Finish          | Electro -Tin Plated |
| Color           | Blue                |
| Wire Range      | 16-14               |

**Dimension Information**

|                     |       |
|---------------------|-------|
| Length (inches)     | .87   |
| Diameter D (inches) | 0.075 |
| Stock Thickness     | .03   |

**Specifications**

|                     |           |
|---------------------|-----------|
| Temperature Rating  | 105°C     |
| Voltage Rating      | 300V      |
| Flammability Rating | UL 94 V-0 |

**Tooling**

- [Tool Charts](#) [Click Here](#)
- [Application Tools](#) [WT1455, ERG4001, ERG4003](#)
- [Recommended Tool](#) [ERG4001](#)

**Packaging**

|                       |                        |
|-----------------------|------------------------|
| Order Multiple        | 100                    |
| Inner Package         | 100                    |
| Outer Package         | 500                    |
| Package Type          | Standard               |
| Package Height        | 6.19                   |
| Package Length        | 3.19                   |
| Package Width         | 2.31                   |
| T&B Sold in UOM       | Each                   |
| T&B Weight Per UOM    | 0.22 lbs. per 100      |
| Alternate Package Qty | <a href="#">RB47PT</a> |

**Application Support**

- [Overview](#) [Click Here](#)
- [Wire Guide Tables](#) [Click Here](#)

**Certifications**

RoHS Compliance Yes [Generate Compliance Certificate](#)

HOME  
[Global Site](#)  
[Report Issue](#)

LOGIN  
[T&B Access \(Dist only\)](#)  
[Suppliers](#)  
[MyTNB](#)

RESOURCES  
[Catalog PDFs](#)  
[End User Toolkit](#)  
[Solution Set Brochures](#)  
[Vertical Market Brochures](#)  
[Where To Buy](#)

SUPPORT  
[Contact Us](#)  
[Global Locations](#)  
[Product Support](#)  
[Tool Services](#)  
[Terms](#)

COMPANY  
[About Us](#)  
[Careers](#)  
[Employees](#)  
[News](#)