

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [39-00-0327](#)  
**Status:** **Active**  
**Overview:** Standard .062"  
**Description:** 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 1560, Male, with Tin (Sn) Plated Brass Contact, 18-24 AWG, Bag

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-1625-010 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">1560</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Standard .062"</a>
Product Name	Standard .062"
UPC	800753330290

**Physical**


Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	123.700/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm <sup>2</sup>	N/A

**Material Info**

Old Part Number 1560TL

**Reference - Drawing Numbers**

Product Specification PS-1625-010, RPS-1625-001, RPS-5025-001  
 Sales Drawing SD-1560-001



Series

image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC**

**Contains SVHC: No Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

1560Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Insertion Tool	<a href="#">0011020001</a>
Manual Extraction Tool	<a href="#">0011030002</a>
Hand Crimp Tool for Standard 1.57mm Pin and Socket Crimp Terminals, 18-24 AWG	<a href="#">0638191300</a>

**Japan**

Description	Product #
Hand Extraction Tool	<a href="#">0011267034</a>

This document was generated on 04/19/2013

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**