

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [50212-8100](#)  
**Status:** **Active**  
**Overview:** [Micro-Latch™](#)  
**Description:** 2.00mm Pitch Crimp Terminal, Female, 24-30 AWG, Bag

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51090-018 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51160-001 (PDF)</a>
<a href="#">Product Specification PS-51065-005 (PDF)</a>	<a href="#">Product Specification PS-51160-006 (PDF)</a>
<a href="#">Product Specification PS-51065-016 (PDF)</a>	<a href="#">Product Specification PS-51225-003 (PDF)</a>
<a href="#">Product Specification PS-51065-017 (PDF)</a>	<a href="#">Product Specification PS-52968-006 (PDF)</a>
<a href="#">Product Specification PS-51065-018 (PDF)</a>	<a href="#">Product Specification PS-52968-007 (PDF)</a>
<a href="#">Product Specification PS-51089-001 (PDF)</a>	<a href="#">Product Specification PS-53717-002 (PDF)</a>
<a href="#">Product Specification PS-51089-005 (PDF)</a>	<a href="#">Product Specification PS-54111-002 (PDF)</a>
<a href="#">Product Specification PS-51090-003 (PDF)</a>	<a href="#">Product Specification PS-54214-001 (PDF)</a>
<a href="#">Product Specification PS-51090-004 (PDF)</a>	<a href="#">Product Specification PS-54452-007 (PDF)</a>
<a href="#">Product Specification PS-51090-005 (PDF)</a>	<a href="#">Product Specification PS-55533-004 (PDF)</a>
<a href="#">Product Specification PS-51090-009 (PDF)</a>	<a href="#">Packaging Specification SPK-50212-001 (PDF)</a>
<a href="#">Product Specification PS-51090-016 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-51090-017 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	<a href="#">50212</a>
Application	Signal
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	<a href="#">Micro-Latch™</a>
Packaging Alternative	<a href="#">50212-8000 (Reel)</a>
Product Name	Mi II™, Micro-Latch™, Sherlock™
UPC	800754369473

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	20.400/mg
Packaging Type	Bag
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	2A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	SPK-50212-001
Product Specification	PS-51065-005, PS-51065-016, PS-51065-017, PS-51065-018, PS-51089-001, PS-51089-005, PS-51090-003, PS-51090-004, PS-51090-005, PS-51090-009, PS-51090-016, PS-51090-017, PS-51090-018, PS-51160-001, PS-51160-006,

*Series image - Reference only*

**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[50212Series](#)

**Use With**

[502351 DuraClik™ Wire-to-Board](#)  
 Receptacle Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Extraction Tool	<a href="#">0011030043</a>
Hand Crimp Tool for 2.00mm Pitch Terminal, 24-30 AWG	<a href="#">0638190500</a>

**Japan**

Description	Product #
Extraction Tool	<a href="#">0571056000</a>
Hand Crimp Tool	<a href="#">0571765000</a>

PS-51225-003, PS-52968-006, PS-52968-007,  
PS-53717-002, PS-54111-002, PS-54214-001,  
PS-54452-007, PS-55533-004, RPS-35507-003,  
RPS-502079-002, RPS-502079-003, RPS-502079-004,  
RPS-502079-005, RPS-502079-006, RPS-502079-007,  
RPS-502079-008, RPS-502079-009, RPS-502079-010,  
RPS-502079-011, RPS-51065-001, RPS-51065-002,  
RPS-51065-006, RPS-51065-007, RPS-51065-010,  
RPS-51065-011, RPS-51065-012, RPS-51065-013,  
RPS-51065-014, RPS-51065-015, RPS-51065-017,  
RPS-51065-018, RPS-51065-019, RPS-51065-021,  
RPS-51065-022, RPS-51065-023, RPS-51065-025,  
RPS-51065-026, RPS-51065-027, RPS-51065-028,  
RPS-51065-030, RPS-51065-031, RPS-51065-032,  
RPS-51089-002, RPS-51089-004, RPS-51089-005,  
RPS-51090-002, RPS-51090-005, RPS-51090-006,  
RPS-51090-008, RPS-51090-009, RPS-51090-010,  
RPS-51090-012, RPS-51090-013, RPS-51090-014,  
RPS-51090-015, RPS-51090-017, RPS-51090-018,  
RPS-51090-019, RPS-51090-021, RPS-51090-022,  
RPS-51090-026, RPS-51160-003, RPS-51160-005,  
RPS-51339-004, RPS-51339-007, RPS-52484-002,  
RPS-52968-005, RPS-52968-012, RPS-52968-013,  
RPS-52969-004, RPS-52969-006, RPS-53324-001,  
RPS-53358-001, RPS-54111-004, RPS-54111-005,  
RPS-54269-004, RPS-55460-011, RPS-87369-001  
SD-50212-001

Sales Drawing

This document was generated on 05/14/2013

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**