

EVERBUILD QUICK DRYING WOOD STAIN



Colour	Product Code	Pack Size	Box Qty
Natural Oak	WSTAINSNO2	2.5ltr	2
	WSTAINSNO07	750ml	6
Antique Pine	WSTAINSPN2	2.5ltr	2
	WSTAINSPN07	750ml	6
Dark Oak	WSTAINSDO2	2.5ltr	2
	WSTAINSDO07	750ml	6
Mahogany	WSTAINSMAH2	2.5ltr	2
	WSTAINSMAH07	750ml	6
Rosewood	WSTAINSRW2	2.5ltr	2
	WSTAINSRW07	750ml	6
Walnut	WSTAINSWAL2	2.5ltr	2
	WSTAINSWAL07	750ml	6

Product Description

Everbuild Quick Drying Wood Stain is a professional, low solvent wood stain that enhances the natural qualities of wood, and provides long lasting protection.

The weatherproof protection provided by Everbuild Wood Stain also gives a crack and peel resistant finish and excellent resistance to ultra violet light degradation.

Ideal for use on smooth planed exterior and interior timber, such as doors, window frames, architectural timbers, conservatories, cladding & garden furniture etc.

Under normal weathering conditions Everbuild Quick Drying Wood Stain can be expected to provide protection for up to 5 Years.

Benefits

- Solvent Free formula
- Up to 5 years protection.
- Internal and external use.
- Touch dry in 30 minutes, overcoat after 4 hours.

Surface Preparation

Ensure wood is clean, dry and free from dirt or dust. Any rough surfaces or areas should be sanded until smooth. Old varnish or paint finishes must be completely removed by sanding or stripping before applying of Everbuild Wood Stain.

Old wood stain finishes should be cleaned and lightly sanded to provide a key before application

Application

Stir product well before use and intermittently during application.

Brush apply Everbuild Wood Stain, always following the direction of the wood grain, approximately 3 coats will be required for full coverage. It is touch dry in 30 minutes, allow to dry for 4 hours in between coats, lightly sand the surface before applying the final coat taking care to only sand very lightly around edges.

Always apply the stain to a wet edge, working systematically across the surface keeping the wet edge moving together as much as possible.

After applying to an area the finished appearance will be improved by feather brushing over the entire area with an unloaded brush taking care to follow the wood grain.

When re-coating on darker shades of stain Everbuild Quick Drying Wood Stain in clear can be used to refresh the coat without further darkening the surface.

Clean brushes with water after use, a little washing up liquid will assist brush cleaning.

Limitations

- Colour swatch label is an indication of the colour of the stain only, **always** test the colour on an inconspicuous, small area before full scale application.
- Do not apply in direct sunlight.
- Do not use on wood floors or decking.
- Protect from frost and do not use in temps below 10°C.
- To avoid risk of spillage, always transport this tin in a secure and upright position.
- Do not apply in direct sunlight.
- As the manufacturer cannot know all the uses its products may be put to, it is the user's responsibility to determine suitability for use. If in doubt, contact Technical Services Department for advice or refer to technical data sheet.

Maintenance

Inspect surfaces every 3 -5 years depending on exposure to weathering and apply top up maintenance coat as required.

Coverage Guide

Up to 20 square metres per litre. Coverage will vary depending on the absorbency of the wood.

Health & Safety

See MSDS for full list of hazards.

Storage

Store in cool dry conditions between + 5 and +25°C. Storage outside these conditions will dramatically reduce shelf life. PROTECT FROM FROST.

Shelf Life

2 years from date of manufacture when stored as directed.

The technical data contained herein is based on our present knowledge and experience and we cannot be held liable for any errors, inaccuracies, omissions or editorial failings that result from technological changes or research between the date of issue of this document and the date the product is acquired. Before using the product, the user should carry out any necessary tests in order to ensure that the product is suitable for the intended application. Moreover, all users should contact the seller or the manufacturer of the product for additional technical information concerning its use if they think that the information in their possession needs to be clarified in any way, whether for normal use or a specific application of our product. Our guarantee applies within the context of the statutory regulations and provisions in force, current professional standards and in accordance with the stipulations set out in our general sales conditions. The information detailed in the present technical data sheet is given by way of indication and is not exhaustive. The same applies to any information provided verbally by telephone to any prospective or existing customer.