

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [501591-3011](#)
Status: **Active**
Overview: SlimStack™ 0.40mm Pitch Board-to-Board Connectors
Description: 0.40mm Pitch SlimStack™ Board-to-Board Receptacle, SMT, Dual Row, Vertical Stacking, 0.90mm Stacking Height, with Solder Tabs, 30 Circuits

Documents:

3D Model	Product Specification PS-501591-003 (PDF)
Drawing (PDF)	Packaging Specification SPK-501591-001 (PDF)
Product Specification PS-501591-002 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E29179

General

Product Family	PCB Receptacles
Series	501591
Application	Board-to-Board, Signal
Overview	SlimStack™ 0.40mm Pitch Board-to-Board Connectors
Product Name	SlimStack™
UPC	822350792004

Physical

Circuits (Loaded)	30
Circuits (maximum)	30
Color - Resin	Black
Durability (mating cycles max)	20
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Mated Height	0.90mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Net Weight	33.841/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.40mm
Polarized to Mating Part	No
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Surface Mount


Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-501591-001
Product Specification	PS-501591-002, PS-501591-003, RPS-501591-007, RPS-501591-010, RPS-501591-011, RPS-501591-012,



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[501591Series](#)

Mates With

[501594 PCB Header](#)

Sales Drawing

RPS-501591-013, RPS-501591-014, RPS-501591-015,
RPS-501591-016, RPS-501591-017, RPS-501591-019,
RPS-501591-020
SD-501591-005, SD-501591-006

This document was generated on 05/03/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION