


Datasheet

V88- TV mounts for LCD and Plasma Televisions

V88-F3720 Fixed Mount 26" to 46" up to 50kg
 V88-F3740 Fixed Mount 26" to 46" up to 40kg
 V88-F6020 Fixed Mount 37" to 60" up to 75kg
 V88-F6040 Fixed Mount 37" to 65" up to 75kg

V88-A2740 Articulated Mount up to 24" up to 18kg
 V88-A3221 Articulated Mount 13" to 32" up to 25kg
 V88-A3710 Articulated Mount 26" to 46" up to 36kg
 V88-A5010 Articulated Mount 37" to 65" up to 60kg

V88-T3710 Tilt Mount 26" to 42" up to 40kg
 V88-T5010 Tilt Mount 37" to 60" up to 75kg



The V88- range of TV and monitor mounts for LCD and plasma screens are high quality well designed brackets for strength and simplicity of installation. LCD mounts are often rarely visible but the high quality ensures that they are easy to fit and adjust to both the back of the screen and to the wall.

Most models incorporate a security fixing and discrete cable management with a spirit level to aid level fixing. All V88 mounts use an electrostatic powder coated finish on steel pressings or aluminium diecasting. Each model is supplied with a kit of suitable screws, washers and spacers to suit the majority of different makes of TV.

When installing it is important to use the correct mount for the application and to ensure that the TV is mounted using the correct supplied screws and spacers, otherwise the screen may be damaged.




V88-F3720	Fixed TV Mount
	For 26" to 46" screen size.
	Maximum load 50kg.
	2.5cm (1") profile.
	400mm x 400mm maximum mounting pattern including VESA standard.
	Lift & Hook design for safety and ease of installation
	Lockable safety and security (padlock not included)
	Min TV Dimension H44 x W42cm Powder coated steel pressing

V88-F3740	Fixed TV Mount
	For 26" to 46" screen size.
	Maximum load 40kg.
	3.0cm (1.2") profile.
	500mm x 400mm maximum mounting pattern including VESA standard.
	Lift & Hook design for safety and ease of installation
	Lockable safety and security (padlock not included)
	Min TV Dimension H53 x W42cm Powder coated steel pressing

In the interests of continued product improvement and development we reserve the right to change specifications, design and dimensions without prior notice. Details correct at date of publication 25/06/2013

Datasheet

V88- TV mounts for LCD and Plasma Televisions cont'd

	V88-F6020	Fixed TV Mount
		For 37" to 60" screen size.
		Maximum load 75kg.
		2.5cm (1") profile.
		800mm x 500mm maximum mounting pattern including VESA standard.
		Lift & Hook design for safety and ease of installation. Spirit Level
		Lockable safety and security (padlock not included) Min TV Dimension H85 x W53cm Powder coated steel pressing
	V88-F6040	Fixed TV Mount
		For 37" to 65" screen size.
		Maximum load 75kg.
		3.0cm (1.2") profile.
		820mm x 500mm maximum mounting pattern including VESA standard.
		Lift & Hook design for safety and ease of installation.
		Lockable safety and security (padlock not included) Min TV Dimension H82 x W50cm Powder coated steel pressing
	V88-A2740	Full Motion Articulated TV Mount Pan, Tilt, Swivel
		For maximum 24" screen size.
		Maximum load 18kg.
		5.5cm to 25cm (2.2" to 9.8) profile
		100mm x 100mm maximum mounting pattern including VESA standard.
		Spirit Level & Cable Management
		Powder coated diecast aluminium / steel pressing
	V88-A3221	Full Motion Articulated TV Mount Pan, Tilt, Swivel, Portrait to Landscape Rotate
		For 13" to 32" screen size
		Maximum load 25kg
		7.9cm to 29.4cm (3.1" to 11.5") profile
		200mm x 200mm maximum mounting pattern including VESA standard.
		Spirit Level & Cable Management
		Powder coated diecast aluminium / steel pressing

In the interests of continued product improvement and development we reserve the right to change specifications, design and dimensions without prior notice. Details correct at date of publication 25/06/2013

Vision Products (Europe) Ltd, Unit 5 Redbourne Park, Liliput Road, Brackmills, Northampton NN4 7DT





Tel: 01604 662748 Fax: 01604 662746 Email: technical@vision-products.co.uk

E&OE ©2013 Vision Products (Europe) Ltd

In the interests of continued product improvement and development we reserve the right to change specifications, design and dimensions without prior notice. Details correct at date of publication 25/06/2013
www.vision-products.co.uk

Datasheet

V88- TV mounts for LCD and Plasma Televisions cont'd

	V88-A3710	Full Motion Articulated TV Mount Pan, Tilt, Swivel
		For 26" to 46" screen size.
		Maximum load 36kg.
		14cm to 42cm (5.5" to 16.5") profile.
		450mm x 400mm maximum mounting pattern including VESA standard
		Lift & Hook design for safety and ease of installation.
		Lockable safety and security (padlock not included)
	Min TV Dimension H45 x W40cm Powder coated steel pressing	
	V88-A5010	Full Motion Articulated TV Mount Pan, Tilt, Swivel
		For 37" to 65" screen size
		Maximum load 60kg
		14cm to 42cm (5.5" to 16.5") profile.
		800mm x 500mm maximum mounting pattern including VESA standard
		Lift & Hook design for safety and ease of installation.
		Lockable safety and security (padlock not included)
	Min TV Dimension H80 x W50cm. Powder coated steel pressing	
	V88-T3710	Tilt Adjustable TV Mount
		For 26" to 42" screen size.
		Maximum load 40kg.
		9cm (3.5") profile.
		450mm x 320mm maximum mounting pattern including VESA standard
		Lift & Hook design for safety and ease of installation. Spirit Level
		Lockable safety and security (padlock not included)
	Min TV Dimension H45 x W32cm. Powder coated steel pressing	
	V88-T5010	Tilt Adjustable TV Mount
		For 37" to 60" screen size
		Maximum load 75kg
		9cm (3.5") profile.
		680mm x 500mm maximum mounting pattern including VESA standard
		Lift & Hook design for safety and ease of installation. Spirit Level
		Lockable safety and security (padlock not included)
	Min TV Dimension H68 x W50cm Powder coated steel pressing	

All mounts are provided with wall fixings suitable for solid walls. Alternative fixings may be required for hollow or partition structures. Check that the structure of the wall is suitable for the weight of the TV or monitor you intend to mount.

In the interests of continued product improvement and development we reserve the right to change specifications, design and dimensions without prior notice. Details correct at date of publication 25/06/2013

Vision Products (Europe) Ltd, Unit 5 Redbourne Park, Liliput Road, Brackmills, Northampton NN4 7DT

Tel: 01604 662748 Fax: 01604 662746 Email: technical@vision-products.co.uk

E&OE ©2013 Vision Products (Europe) Ltd

Company Reg No: 05044212

www.vision-products.co.uk

