



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: BP48V242UTAA

### TAA Compliant External Battery Pack for select UPS Systems

#### Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Extends runtime of select compatible Tripp Lite UPS Systems with 48VDC external battery connector
- Simple installation; 2U rackmount, tower and stack adaptable



#### Description

BP48V242UTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. This rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite systems. Multi-use form factor supports configuration in stacking, upright tower and rackmount applications using only 2 rack spaces (2U). Includes heavy gauge cabling with high current DC connector for simple installation.

Compatible UPS Systems - SM2200RML2UTAA, SM3000RML2UTAA, SMX2200RTL2UTAA, SMX2200RT2UTAA, SMX3000RT2UTAA and other Tripp Lite UPS systems that specify the use of this battery pack.

#### Applications

- Ideal means of lengthening the battery runtime provided by compatible Tripp Lite UPS systems. Battery pack may be ordered at time of original UPS purchase or sourced at a later date to extend runtime performance if site power conditions deteriorate and longer battery runtime is desired.

#### Package Includes

- BP48V242UTAA TAA Compliant External Battery Pack
- Mounting hardware
- Warranty information
- Instruction manual

#### Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.
- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 2 rack spaces (2U)
- Includes heavy gauge cabling with high current DC connectors for simple installation
- NOTE: LIMIT OF 1 BP48V242UTAA PER UPS, USE BP48V60RT3UTAA FOR MULTI-PACK COMPATIBILITY

#### Specifications

<b>BATTERY</b>
----------------

DC system voltage (VDC)	48
Connects to UPS via	Attached cable with blue 175 amp male DC connector
Typical battery lifespan	4-6 years typical (North America)
<b>PHYSICAL</b>	
Shipping Dimensions (HWD/in)	7.25 x 23.5 x 18.5
Shipping Dimensions (HWD/cm)	18.4 x 59.7 x 47
Shipping weight (lbs)	70
Shipping weight (kg)	31.8
Unit Dimensions (HWD/in)	3.5 x 17.5 x 13.5
Unit Dimensions (HWD/cm)	8.9 x 44.5 x 34.3
Unit weight (lbs)	63
Unit weight (kg)	28.6
Form factors supported	2U rack/tower
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL, cUL, CE, NOM, TAA Compliant
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	3 year, 5 year, next day and on-site warranty coverage available

## Related Items

### Optional Products

Related Model	Description	Qty.
<a href="#">WEXT3-BP48V24</a>	3-Year Extended Warranty - For BP48V24-2U and BP48V242UTAA Battery Packs	1
<a href="#">WEXT5-BP48V24</a>	5-Year Extended Warranty - For BP48V24-2U and BP48V242UTAA Battery Packs	1
<a href="#">2-9USTAND</a>	Enables Tower Placement of Rackmount UPS Systems	1
<a href="#">2POSTRMKITWM</a>	Enables 2-Post Rackmount or Wallmount Installation of Select Rackmount UPS Systems	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4376](http://www.tripplite.com/en/products/model.cfm?txtModelID=4376).

