



G3 Kleen-It Cleaner/Lubricant

2421

Techspray offers a variety of specialty chemicals for plant maintenance. Products range from surface cleaners, equipment service chemicals, lubricants, and adhesives.



Non-flammable cleaner and lubricant

Techspray's precision lubricants are specifically designed to clean, lubricate, and protect electronic and electromechanical devices. Silicone based and can be used as a general light lubricant, displace water, and waterproof. Patented, non-flammable G3 formula cleans oxides, grease, and other contamination as it lubricates.

- Non-flammable
- Non-ozone depleting
- Cleans as it lubricates
- Displaces water
- Waterproofs

Product Packaging

2421-12S
G3 Kleen-It Cleaner/Lubricant
12 oz
12 units/case





Technical Information

Chemical & Physical Properties

Appearance	Clear, mobile liquid
Odor	Faint ethereal odor
Flash Point	none
Density	1.24 at 19.4°C

Chemical Composition

CHEMICAL NAME	CAS #
Siloxanes and Silicones, di-Me	63148-62-9
1,2-transdichloroethylene	156-60-5
1,1,1,3,3-Pentafluoropropane	460-73-1
WHITE MINERAL OIL	8042-47-5
1,1,1,2-Tetrafluoroethane	811-97-2

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW



Techspray
P.O. Box 949, Amarillo, TX 79105
800-858-4043 • www.techspray.com

