

2722

Lamps with glass wedge bases for cars



Product benefits

- Wide product range
- Reliable quality

Product features

- Original spare parts

Technical data


Electrical data

| | |
|-----------------------|--------|
| Power input | 2 W |
| Nominal wattage | 2 W |
| Nominal voltage | 12 V |
| Power input tolerance | ±15 % |
| Test voltage | 13.5 V |

Light technical data

| | |
|-------------------------|-------|
| Luminous flux | 12 lm |
| Luminous flux tolerance | ±20 % |

Dimensions & weight



Product line drawing

| | |
|----------------|---------|
| Length | 20.0 mm |
| Diameter | 5.0 mm |
| Product weight | 0.40 g |

Lifespan

| | |
|-------------|--------|
| Lifespan B3 | 1300 h |
| Lifespan Tc | 4000 h |

Additional product data

| | |
|-----------------------------|---------|
| Base (standard designation) | W2x4.6d |
|-----------------------------|---------|

Certificates & standards

Product datasheet

| | |
|---------------------|---|
| ECE category | - |
|---------------------|---|

Country specific categorizations

| | |
|------------------------|------|
| Order reference | 2722 |
|------------------------|------|

Country specific information

| Product code | METEL code | SEG-No. | STK-Number | UK Org |
|---------------------|-------------------|----------------|-------------------|---------------|
| 4008321094803 | OSRA2722 | - | - | - |
| 4050300925783 | OSRA2722BLI2 | - | - | - |

Product datasheet

Logistical Data

| Product code | Product description | Packaging unit (Pieces/Unit) | Dimensions (height x width x length) | Volume | Gross weight |
|---------------|---------------------|------------------------------|--------------------------------------|----------------------|--------------|
| 4008321094803 | 2722 | Unpacked 1 | 10 mm x 7 mm x 28 mm | 0.00 dm ³ | 5.17 g |
| 4008321094810 | 2722 | Folding carton box 10 | 99 mm x 47 mm x 41 mm | 0.19 dm ³ | 15.01 g |
| 4008321094827 | 2722 | Shipping carton box 50 | 115 mm x 55 mm x 148 mm | 0.94 dm ³ | 105.05 g |
| 4050300925783 | 2722 | Blister 2 | 36 mm x 7 mm x 78 mm | 0.02 dm ³ | 8.67 g |
| 4008321140333 | 2722 | Shipping carton box 20 | 80 mm x 105 mm x 137 mm | 1.15 dm ³ | 102.67 g |

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.