

Self-Sticking Pipe Markers

www.BradyID.com/pipemarkers



B-946 Self-Sticking Vinyl Pipe Markers

- Markers meet the requirements of the ASME (ANSI) A13.1 Standard for the identification of piping system contents when used with Directional Flow Arrow Tape
- Durable B-946 material ideal for indoor and outdoor environments
- Supplied on a coated backing material that makes handling and installation easy
- Recommended to use Directional Flow Arrow Tape to indicate flow direction

How to order:

1. Choose the desired pipe marker legend below.
2. Replace the asterisk (*) with the style code from the chart on the right (1, 1HV, 3C or 4) to indicate your desired pipe marker size and style. (Example: Air = 7005-3C)

Style and Size Chart

Style Code	Outside Diameter	Letter Height	Style Description	Style Example
Style: 1	2-1/2" to 7-7/8"	2"	One 2-1/4" x 14" marker per card	HEATING RETURN
Style: 1HV	8" or greater	3-1/2"	One 4" x 24" marker per card	HEATING RETURN
Style: 3C	less than 34"	1/2"	Three 2-1/4" x 2-3/4" markers per card plus 8 strips of Arrow Tape	
Style: 4	34" to 2-38"	3/4"	Four 1-1/8" x 7" markers per card	FIRE AUTO SPRINKLERS FIRE AUTO SPRINKLERS FIRE AUTO SPRINKLERS FIRE AUTO SPRINKLERS

Self-Sticking Legends Chart

Catalog Number	Legend	Bkgd Color	Catalog Number	Legend	Bkgd Color	Catalog Number	Legend	Bkgd Color
7005 -*	AIR	Yellow	7089 -*	DOMESTIC HOT WATER SUPPLY	Yellow	7212 -*	PLANT AIR	Yellow
7006 -*	AIR	Blue	7090 -*	DRAIN	Green	7218 -*	POTABLE WATER	Yellow
7007 -*	AIR	Green	7107 -*	FIRE AUTO SPRINKLERS	Red	7224 -*	PROCESS WATER	Green
7010 -*	AIR SUPPLY	Blue	7110 -*	FIRE PROTECTION WATER	Red	7227 -*	PROPANE GAS	Yellow
7014 -*	AMMONIA	Yellow	7115 -*	FUEL OIL	Yellow	7229 -*	RAIN WATER	Green
7015 -*	ARGON	Green	7119 -*	GAS	Yellow	7235 -*	REFRIGERANT LIQUID	Yellow
7017 -*	ASBESTOS FREE	Blue	7121 -*	GLYCOL	Yellow	7242 -*	RETURN	Green
7018 -*	ASBESTOS FREE INSULATION	Blue	7122 -*	GLYCOL RETURN	Yellow	7244 -*	RETURN	Yellow
7019 -*	ASBESTOS INSULATION	Yellow	7123 -*	GLYCOL SUPPLY	Yellow	7247 -*	ROOF DRAIN	Green
7025 -*	BLANK	Yellow	7125 -*	HEATING RETURN	Yellow	7250 -*	SANITARY SEWER	Green
7045 -*	CHILLED WATER	Green	7127 -*	HEATING SUPPLY	Yellow	7251 -*	SANITARY SEWER	Yellow
7046 -*	CHILLED WATER RETURN	Green	7128 -*	HEATING WATER	Yellow	7252 -*	SANITARY VENT	Yellow
7047 -*	CHILLED WATER SUPPLY	Green	7129 -*	HEATING WATER RETURN	Yellow	7253 -*	SANITARY WASTE	Yellow
7054 -*	CITY WATER	Green	7130 -*	HEATING WATER SUPPLY	Yellow	7267 -*	SPRINKLER	Red
7055 -*	COLD WATER	Green	7137 -*	HIGH PRESSURE CONDENSATE	Yellow	7268 -*	SPRINKLER FIRE	Red
7058 -*	COMPRESSED AIR	Yellow	7146 -*	HOT WATER	Yellow	7269 -*	SPRINKLER WATER	Red
7059 -*	COMPRESSED AIR	Green	7147 -*	HOT WATER RECIRCULATION	Yellow	7270 -*	STEAM	Yellow
7060 -*	COMPRESSED AIR	Blue	7148 -*	HOT WATER RETURN	Yellow	7273 -*	STORM DRAIN	Green
7061 -*	CONDENSATE	Yellow	7149 -*	HOT WATER SUPPLY	Yellow	7274 -*	STORM SEWER	Green
7062 -*	CONDENSATE DRAIN	Yellow	7163 -*	INDUSTRIAL WATER	Green	7282 -*	SUPPLY	Green
7063 -*	CONDENSATE DRAIN	Green	7175 -*	LOW PRESSURE CONDENSATE	Yellow	7311 -*	SUPPLY	Yellow
7065 -*	CONDENSATE RETURN	Yellow	7179 -*	LOW PRESSURE STEAM	Yellow	7283 -*	TEMPERED WATER	Yellow
7067 -*	CONDENSER WATER	Green	7184 -*	MEDICAL AIR	Yellow	7285 -*	TOWER WATER	Green
7068 -*	CONDENSER WATER RETURN	Green	7186 -*	MEDICAL VACUUM	White	7291 -*	VACUUM	Yellow
7069 -*	CONDENSER WATER SUPPLY	Green	7190 -*	MEDIUM PRESSURE NATURAL GAS	Yellow	7292 -*	VACUUM	Green
7070 -*	COOLING WATER	Green	7196 -*	NATURAL GAS	Yellow	7295 -*	VENT	Yellow
7071 -*	COOLING WATER RETURN	Green	7198 -*	NITROGEN	Green	7296 -*	VENT	Green
7073 -*	DEIONIZED WATER	Green	7200 -*	NITROGEN	Blue	7298 -*	WASTE	Yellow
7084 -*	DOMESTIC COLD WATER	Green	7203 -*	NON-POTABLE WATER	Yellow	7299 -*	WASTE	Green
7086 -*	DOMESTIC COLD WATER SUPPLY	Green	7208 -*	OVERFLOW	Yellow	7303 -*	WATER	Yellow
7087 -*	DOMESTIC HOT WATER	Yellow	7210 -*	OXYGEN	Green	7304 -*	WATER	Green
7088 -*	DOMESTIC HOT WATER RETURN	Yellow	7209 -*	OXYGEN	Yellow			

Spanish Legends Chart

Legend	Bkgd Color	Style 1HV	Style 1	Style 4	Style 3C	Legend	Bkgd Color	Style 1HV	Style 1	Style 4	Style 3C
AGUA	Green	83596	83540	83576	83615	DESAGUE SANITARIO	Green	83589	83527	83563	-
AGUA DE REFRIGERACION	Green	83484	83424	83460	-	GAS	Yellow	83489	83432	83468	83505
AGUA FRIA	Green	-	83418	83453	83498	GAS NATURAL	Yellow	83585	83517	83553	83601
AGUA POTABLE	Yellow	-	83522	83558	-	HIDROGENO	Yellow	-	83510	83545	83598
AGUA REFRIGERADA	Green	83477	83414	83449	-	OXIGENO	Green	-	83520	83556	83604
AGUA PROTEC. PAPA INCENDIOS	Red	-	83430	83466	-	RESPIRADERO	Yellow	-	83537	83573	83612
AIRE	Blue	-	83400	83436	-	RETORNO DE AGUA REFRIGERADA	Green	83478	83415	83450	-
AIRE COMPRESIDO	Blue	-	83421	83456	83501	SUMINISTRO AGUA REFRIGERADA	Green	83479	83416	83451	-
AIRE USO MEDICO	Yellow	-	83514	83550	83599	VACIO USO MEDICO	White	-	83515	83551	83600
CAUSTICA	Yellow	-	83413	83448	83496	VAPOR	Yellow	83590	83530	83566	83607