

Panel mounting frames - VS-PPC-F1-RJ45-POBK-1R-F - 1608197

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 panel mounting frame, IP67, for push-pull interlocking, plastic, with the Freenet system, for square panel cutout, with grommet, without mounting screws



Key commercial data

Packing unit	1 pc
GTIN	4 046356 159937
Weight per Piece (excluding packing)	8.4 g
Custom tariff number	85389099
Country of origin	Germany
Product key	ABNADE
Note	Made to Order (non-returnable)

Technical data

Mechanical characteristics

Locking type	Push Pull
Insertion/withdrawal cycles	≥ 500
Color	black

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Degree of protection	IP65/IP67

Material data

Inflammability class according to UL 94	V0
Housing material	PA-GF
Material	Plastic
Sealing material	NBR
Seal material	NBR

Electrical characteristics

Panel mounting frames - VS-PPC-F1-RJ45-POBK-1R-F - 1608197

Technical data

Electrical characteristics

Pollution degree	2
------------------	---

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002310

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Accessories

Accessories

Female insert

RJ45 socket insert - VS-08-BU-RJ45-5-F/PK - 1652936



RJ45 socket insert, for the Freenet system, CAT5e, 8-pos., shielded, with cable connection (IDC fast connection), for solid wires AWG 24 ... 22

Panel mounting frames - VS-PPC-F1-RJ45-POBK-1R-F - 1608197

Accessories

RJ45 socket insert - VS-08-BU-RJ45-6-F/PK - 1652949



RJ45 socket insert, for the Freenet system, CAT6, 8-pos., shielded, with cable connection (IDC fast connection), for litz and solid wires AWG 24 ... 22

Rectangular connector (device side)


RJ45 socket insert - VS-08-BU-RJ45-5-F/BU - 1652952




RJ45 socket insert, for the Freenet system, CAT5e, 8-pos., shielded, socket on socket

Drawings

Dimensioned drawing



Dimensioned drawing



Panel cutout

Push-Pull panel mounting frame, Freenet system, IP67