

# MASTER<sup>®</sup> APPLIANCE

Designers and Manufacturers of Heat Tools for Industry

## Master Varitemp<sup>®</sup> Heat Guns



*Deluxe Varitemp Heat Gun*

*Varitemp Heat Gun*

- Varitemp Heat Guns use a powerful motor driven blower and durable electric heating element to produce a reliable stream of heated air. Power ratings up to 1,000°F /540°C at 1740 watts (120V) with air flow at 23 CFM means jobs get done faster.
- Made in the USA, these heavy duty, industrial quality heat guns offer the handiest, safest way to get fast, variable temperature flameless heat needed for thousands of uses in the factory, laboratory or workshop.
- Two unique Varitemp Heat Gun stand types, along with an exclusive electronic temperature control, enable you to easily find the right operating position and temperature for the most effective results for your application.
- A broad range of optional attachments make the Master Varitemp Heat Gun ideal for a wide variety of heating, shrinking and drying applications.

# Varitemp® Heat Guns

## Deluxe Varitemp Heat Gun with versatile pivoting stand

Stable, heavy-duty, circular metal stand with non-slip rubber feet. Adjustable handle and spring loaded slide grip gives you multiple pivoting angles for better balance and aim.

### Varitemp Heat Gun Features:

- Variable temperature control provides easy dial-in temperature adjustment from ambient to 1000°F/540°C at 1740 watts
- High air flow rating: 23 CFM at 3000 FPM gets the job done fast
- Powerful high speed universal motor
- Sturdy die-cast aluminum housing
- Double protected heating element housing
- Easily replaceable, reinforced, mica-insulated ceramic heating element
- Externally accessible carbon brush holders for quick replacement
- Three position "OFF-COLD-HOT" rocker switch or "Momentary Contact Safety Switch"
- 6 foot, 3-wire grounded cordset made with flexible, oil and sunlight resistant rubber jacket
- UL and CUL Listed. Made in USA
- Use to shrink tubing and packaging, bend plastics, cure adhesives, dry and heat parts, strip paint, defrost frozen pipes, heat sensitive materials, solder/desolder and more



Pivoting handle and slide grip  
with removable stand



Ergonomic handle with spring  
loaded slide grip



Invert heat gun in the stand to  
lower profile for hands-free use



Spring loaded switch powers unit  
when held by operator

### ORDERING INFORMATION

MASTER DELUXE VARITEMP® HEAT GUN							REPLACEMENT ELEMENT	
MODEL NO.	DESCRIPTION							
VTS-750	Amb.-1000°F	Amb.-540°C	120V	60 Hz	14.5A	1740W	HAS-043K	
VTS-752	Amb.-750°F	Amb.-400°C	220V	50 Hz	7A	1680W	HAS-014K	
MASTER VARITEMP® HEAT GUN								
VT-750C	Amb.-1000°F	Amb.-540°C	120V	60 Hz	14.5A	1740W	HAS-043K	
VT-752C	Amb.-750°F	Amb.-400°C	220V	50 Hz	7A	1680W	HAS-014K	
MASTER VARITEMP® HEAT GUN KIT								
VT-750CK	Amb.-1000°F	Amb.-540°C	120V	60 Hz	14.5A	1740W	HAS-043K	
VT-752CK	Amb.-750°F	Amb.-400°C	220V	50 Hz	7A	1680W	HAS-014K	
MASTER VARITEMP® HEAT GUN with MOMENTARY CONTACT SAFETY SWITCH								
VT-750C-MC	Amb.-1000°F	Amb.-540°C	120V	60 Hz	14.5A	1740W	HAS-043K	
VT-752C-MC	Amb.-750°F	Amb.-400°C	220V	50 Hz	7A	1680W	HAS-014K	



Replacement Heating Element



Brush, Spring and Cap Kit  
Part Number 35257

# Original Varitemp® Heat Gun with rotating stand

Original Varitemp Heat Guns have a traditional non-slip rubber-backed stand with 90° rotation and contoured, well balanced handle.

See “Varitemp Heat Gun Features” on opposite page for other product details.


The Industrial Heat Gun was invented and introduced by Master Appliance in 1958. These rugged die-cast aluminum body heat guns set the quality standards for professional users. Easily replaceable parts and accessories help make your Master Heat® Tool a reliable partner in your success.



UL US  
120V Models



Variable Temperature Control



Rotating Swivel Stand



**Varitemp Heat Gun Kits include:**  
Heat Gun, Reducer 51544, Spreader 51543, Reflector A-160-HG and Carrying Case 51013

### Specifications

- Air Volume: 23 CFM • Air Velocity: 3000 FPM • Motor: Universal • Nozzle Opening: 1.2" I.D., 1.5" O.D.
- Cordset: 6 ft., 3-wire grounded • Dimensions: 9" L x 5.2" W x 10.1" H • Tool Net Weights: VTS: 5 lbs., VT: 3.7 lbs. • Shipping Weights: VTS: 7 lbs., VT: 5 lbs., Heat Gun Kit: 10 lbs.

**Protect, store and carry your Varitemp Heat Gun** and attachments in this rugged case. A well cared for Varitemp Heat Gun will provide years of service. Durable construction along with user replaceable heating elements and motor brushes mean your heat gun will be ready for work.




# Varitemp® Options & Accessories

Professional quality attachments and accessories add versatility to your Varitemp Heat Gun for better results.

Note: For 230 Volt Varitemp Heat Guns destined outside North America, add suffix A1 or A6 to model number to designate plug type.

Example: VT-752C-A1 (India & others)

VT-752C-A6 (Hong Kong, Singapore & others)



**A-160-HG**  
Shrink attachment for tubing up to 3/4"



**51543**  
2-1/4" Spreader attachment



**51544**  
7/8" Reducer attachment



**A-170-HG**  
Shrink attachment for tubing 3/4" to 2" O.D.



**30202**  
Solder preform attachment



**51309**  
3/8" Pinpoint attachment



**51542**  
Glass protector attachment



Get all 3!  
**35245**  
Three of our most popular attachments



**51013**  
Molded storage and carrying case for VT Heat Guns only

## Professional Quality Varitemp Heat Guns. Perfect for many jobs.



Activate Adhesives



Solder/Desolder



Laboratory Precise Heat



Thaw Frozen Pipes



Bend Plastics and PVC




Remove Decals




Strip Paint



Loosen Bolts



Heat Shrink Tubing



Desolder

As with all electrical equipment and tools, for your safety, read the instruction manual before using.

All information including illustrations, is believed to be reliable. Users, however, should independently evaluate the suitability of this product for their application. The only obligations of Master Appliance are those in the Standard Terms and Conditions of Sale for this product. In no case will Master Appliance be liable for any incidental indirect, or consequential damages arising from the sale, resale, use or misuse of this product.

USA  
MADE IN

**MASTER**  
APPLIANCE  
Designers and Manufacturers of Heat Tools for Industry

FOR MASTER PRODUCTS CONTACT: