



Capsuleline

Capsuleline 20W G4 12V CL 2000h 1CT

Single-ended low-voltage halogen capsule giving crisp white halogen light

Product data

• General Characteristics

Philips Code	14729
Cap-Base	G4
Cap-Base Information	na [-]
Bulb	T3 [T3: .354 inch / 9 mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Nominal Lifetime	2000 hr
Rated Lifetime	2000 hr
Rated Lifetime (years)	2 an

• Light Technical Characteristics

Colour Rendering Index	100 Ra8
Colour Temperature	2800 K
Colour Temperature Technical	2750 K
Lamp Luminous Flux	255 Lm
Rated Luminous Flux	255 Lm
Lamp Luminous Efficacy	12.5 Lm/W
LLMF - end nominal lifetime	80 (min) %

• Electrical Characteristics

Rated Wattage	20.0 W
Lamp Wattage	20 W
Technical Lamp Power	20 W
Power Factor	1 -
Voltage	12 V
Lamp Current	1.67 A
Dimmable	yes
Starting Time	0.0 s

Warm-up Time to 60% Light Outp instant full light

• Environmental Characteristics

Energy Efficiency Label (EEL)	C
Energy consumption kWh/1000h	21 kWh

• Measuring Conditions

Switching cycle 8000X

• Luminaire Design Requirements

Pinch Temperature	350 (max) C
Bulb Temperature	220 (max) C

• Product Dimensions

Overall Length C	33 (max) mm
Diameter D	10 (max) mm
Light Center Length L	22 mm

• Product Data

Order code	412997 50
Full product code	871150041299750
Full product name	Capsuleline 20W G4 12V CL 2000h 1CT
Order product name	Caps 20W G4 12V CL 2000h 1CT/10X10F
Pieces per pack	1
Packing configuration	10X10F
Packs per outerbox	100


PHILIPS

Capsuleline

Bar code on pack - EAN1 8711500412997
Bar code on intermediate packing - EAN2 2005040004887
Bar code on outerbox - EAN3 8711500425812


Logistic code(s) - 12NC 924892017111
ILCOS code HSG/C/UB-20-12-G4
Net weight per piece 0.001 kg

Dimensional drawing



Capsuleline 20W G4 12V CL 2000h 1CT

Product	C (Max)	D (Max)	L (Norm)
CAP Fighter 14729 20W G4 12V CL	33	10	22



G4



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 25
data subject to change