

## Universal Reversible USB 2.0 Hi-Speed Cable (Right/Left Angle Reversible A to Reversible A M/M), 3-ft.

MODEL NUMBER: UR020-003-RA



### Highlights

- 3ft, USB 2.0, Right / Left Angle Male-to- Straight Male
- Universal, Reversible connector allows plugging in any direction

### System Requirements

- Computer with USB A-Female port
- USB device or Patch port with USB A-Female port

### Package Includes

- 3ft, USB 2.0, Right / Left Angle Male-to-Straight Male Universal / Reversible Cable

### Description

Easily connect USB devices without fumbling with the connector. Tripp Lite Reversible USB cables have connectors that work in either direction, so you don't have to look to see which is right-side-up anymore.

#### Notes:

1. USB Male-to-Male cable is not a standard USB cable configuration, and is only used in rare instances where a peripheral or patch bay employs a USB A-Female connection, in place of USB B-type port.
2. This cable will not work as a PC-to-PC connection. File sharing between computers requires special, software-driven file transfer cables, such as Tripp Lite [U233-006-PP-R](#) or [U233-006-MP-R](#).

### Features

- 3ft USB 2.0 Right / Left Angle Male-to-Straight Male, with Universal / Reversible connectors
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold contacts and molded ends provide a lifetime of use

## Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	Yes



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Style	USB
Cable Types	USB
<b>OUTPUT</b>	
USB Charging	No
<b>INPUT</b>	
Cable Length (ft.)	3
Cable Length (m)	0.91
<b>PHYSICAL</b>	
Color	Black
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
<b>CONNECTIONS</b>	
Connector A	REVERSIBLE USB A (MALE)
Connector B	REVERSIBLE USB A (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.