

Simply Silent™ Contour CV Product information


Xpelair Simply Silent™ Contour CV Range

MODELS

CV4S	92968AW	Square DC constant volume bathroom fan
LVCV4S	92970AW	Square DC constant volume bathroom fan with external transformer
CV4R	92969AW	Round DC constant volume bathroom fan
LVCV4R	92971AW	Round DC constant volume bathroom fan with external transformer

ANCILLARIES

SSSB	92957AW	Replacement Simply Silent™ Square Baffle
SSRB	92958AW	Replacement Simply Silent™ Round Baffle
SSWKWR	92991AW	Simply Silent™ Wall Kit Round/White
SSWKWS	92992AW	Simply Silent™ Wall Kit Square/White
SSWKBR	92993AB	Simply Silent™ Wall Kit Round/Brown
SSWKBS	92994AB	Simply Silent™ Wall Kit Square/Brown
SSWIN	92996AA	Simply Silent™ Window Kit
SSAK	93061AA	Simply Silent™ 100-150mm Adaptor



4"/100mm constant volume extractor fan for the effective control of humidity, odours and mould growth in bathrooms, shower rooms, cloakrooms, toilets and kitchens.



The Xpelair Simply Silent™ Contour CV range is a family of dMEV fans, meaning that they operate in a trickle mode, constantly ventilating the property but with a boost facility to automatically increase the airflow when required by the integrated active humidity sensor or when manually operated from a remote switch such as the lighting circuit.

The Simply Silent™ Contour CV range uses Intelligent Adaptiflow™ Sensing to deliver constant volume performance. This is achieved by continuously measuring the airflow inside the fan. When the technology senses changes in airflow, brought about by reduced ducting efficiency or a strong wind applying back pressure in the duct, it adapts the fan speed intuitively to maintain a constant volume of extracted air.

The fan has both bathroom and kitchen fan speed settings selected via a single 'jumper' at install. A simple adaptor kit allows this 4" 100mm fan to directly replace any 6" 150mm kitchen fan.

	Airflow (l/s)		Sound (dBA@3M)		Power (W)		SFP (W/l/s)		IPX Rating
	Bathroom	Kitchen	Bathroom	Kitchen	Bathroom	Kitchen	Bathroom	Kitchen	
CV4S	5/8/18	8/13/18	TBC	TBC	1.6/1.9/2.9	1.9/2.3/2.9	0.32/0.24/0.16	0.24/0.18/0.16	4
CV4R	5/8/18	8/13/18	TBC	TBC	1.6/1.9/2.9	1.9/2.3/2.9	0.32/0.24/0.16	0.24/0.18/0.16	4
LVCV4S	5/8/18	8/13/18	TBC	TBC	2.0/2.3/3.7	2.3/3.1/3.7	0.40/0.29/0.21	0.29/0.24/0.21	5
LVCV4R	5/8/18	8/13/18	TBC	TBC	2.0/2.3/3.7	2.3/3.1/3.7	0.40/0.29/0.21	0.29/0.24/0.21	5

The Simply Silent™ Contour CV range features a datalogger designed to help landlords and local authorities avoid damage to their housing stock through condensation and mould. The datalogger records the fan's daily use which can be gathered and interpreted by a technician. This supplies the property owner with information on whether a fan has been operating or whether a tenant has switched it off.

Simply Silent™ Contour CVLV Low Volt models offer complete peace of mind as they are specifically designed to be installed directly in or over the splash area zone 1 in complete safety. The models are supplied with a 24V SELV transformer which is sited out of reach of any person using the bath or shower.



Newcombe House, Newcombe Way
Orton Southgate, Peterborough
United Kingdom, PE2 6SE


t 0844 372 7761
f 0844 372 7762
www.xpelair.co.uk




X106

Improving population health and well-being with innovative and energy efficient indoor air quality and air comfort solutions.







So Simple Installation Fuss-free fitting




Twist and clip cover



Radial fixing points and level reference line



Larger cable access



Screwless hook and clip cover

The flexible Simply Silent™ Contour CV suits wall, ceiling, panel or window installations. So Simple Installation makes fitting quick and hassle free – wherever it's positioned.

It's all thanks to a range of clever features – like the built-in So Simple quick-fit clamp that allows the fan to be secured to ceilings and panels without the need for screws. Larger cable access slots enable easy wiring.

Three adjustable radial screw fixing points and level reference line ensure flexible and accurate fan alignment on vertical surfaces. The duct is strengthened to avoid breakage and distortion during installation. Plus, the Simply Silent™ Contour CV has a hook and clip fan cover – no screws.

Simply Silent™ CV With Ghost™ Air Movement Technology



The Simply Silent™ Contour CV range features unique, innovative Ghost™ Air Movement Technology to deliver near-silent running.

Ghost™ Air Movement Technology uses long-life silent running motors and precision engineered components to avoid mechanical noise whilst advanced air flow management eliminates irregular air flow paths and turbulence.

Features and Benefits



Simply Silent™

Near-silent running minimises disturbance from noisy bathroom fans for a peaceful night's sleep.



Simply Beautiful

The stylish fascia – available in square or round – blends seamlessly with the surrounding decor.



So Simple Installation

A range of smart and innovative features enables a quick, simple and hassle-free installation.



So Simple Maintenance

The smooth fascia acts as a protective shield against grime and may be removed with ease for cleaning.



Compliant

The Simply Silent™ Contour CV range complies fully with Building Regulations Part F and Part L.



IPX rating

The Simply Silent™ Contour CV is IPX4 rated, suitable for safe installation in bathrooms. LVCV models are IPX5 rated.



Five-year warranty

Every Simply Silent™ Contour CV bathroom fan motor comes with a five-year UK warranty.

Simply Silent™ Wall Kit

The revolutionary Simply Silent™ wall kit allows fitting of the outer grille from the inside. Simply push the folded grille through the walltube and pull the attached string back to secure on the outside wall. Available in four different grille designs, the kit comes complete with walltube.

