

QO® Load Centers

Accessories

Class 1130





www.SquareD.com

For the most up-to-date information

QO Load Center Accessories

	Description	Catalog Number	Price	Schedule
Retaining Kit	Secures circuit breaker to interior when used as a back-fed main. For QO612L100F/S, RB, QO612L100DF/S, QO816L100F/S, RB, QO816L100DF/S and QO148L125GF/S, GRB load centers	PK2MB	4.80	DE3A
	Secures 3-pole circuit breaker without accessories to left side of interior when used as a back-fed main. For 3Ø load centers	PK3MB	9.80	DE3A
	Secures circuit breaker to interior when used as a back-fed main for 2-pole QO 150–200 A circuit breakers.	PK5RK	9.80	DE3A
	Secures ONE circuit breaker with or without electrical accessories to right side of interior when used as a back-fed main. For 1Ø 100–125 ampere convertible main load centers. Series S01 and S02.	PK4MB2LA	9.80	DE3A
	Secures ONE circuit breaker with or without electrical accessories to right side of interior when used as a back-fed main. For 1Ø 150–225 ampere convertible main load centers. Series S01 and S02.	PK4MB2HA	9.80	DE3A
Manual Transfer Equipment Kit	For interlocking the handles of two 2-pole or one 2-pole and one 1-pole QO and Q1 circuit breakers mounted side-by-side so that only one circuit breaker can be "ON" at a time	QO2DTI	16.60	DE2E
	QO2DTI mechanical interlock attachment with retaining kits for securing two adjacent back-fed circuit breakers in dual power supply applications. Can be used with (2) 2-poles or (1) 2-pole and (1) 1-pole QO circuit breakers in QO816L100 load centers.	QO2DTIM	42.00	DE2E
	Secures TWO 2-pole circuit breakers to right side of interior when used as back-fed mains, a QO2DTI Kit included for back-up power supply applications. For 1Ø 100–125 ampere convertible main load centers. Series S01 and S02.	PK4DTIM4LA	68.00	DE3A
	Secures TWO 2-pole circuit breakers to right side of interior when used as back-fed mains, a QO2DTI Kit included for back-up power supply applications. For 1Ø 150–225 ampere convertible main load centers. Series S01 and S02.	PK4DTIM4HA	68.00	DE3A
	Secures TWO 2-pole circuit breakers to left side of interior when used as back-fed mains, a QO2DTI Kit included for back-up power supply applications. For 1Ø 100–125 ampere convertible main load centers. Series S01 and S02.	PK4DTIM4LAL	68.00	DE3A
Generator Circuit Breaker Interlock Kit	For use on "G" and "S" Series NEMA 1 and "G" and "S1" Series NEMA 3R load centers. Interlocks a QOM2 2-pole main circuit breaker of a load center (150–225 A) with a QO 2-pole (15–125 A) branch circuit breaker. Includes a retaining kit.	QOCGK2	70.00	DE3A
	For use on "S2" Series NEMA 3R load centers. Interlocks a QOM2 2-pole main circuit breaker of a load center (150–225 A) with a QO 2-pole (15–125 A) branch circuit breaker. Includes a retaining kit.	QORBGK2	70.00	DE3A
Miscellaneous				
Cover Sealing Strap:	Provides means of sealing trim mounting screws on QO load center covers	QO1SE	2.40	DE3A
Surge Arresters:	For use on 1Ø3W, 150 Vac maximum.	SDSA1175	61.00	DE1B
	For use on 3Ø4W, 650 Vac maximum.	SDSA3650	165.00	DE1B
Surge Arrester Mounting Kit:	QO Surgebreaker cUL _{US} Listed Secondary Surge Arrester 150 Vac line-to-ground maximum.	QO2175SB	106.00	DE1B
	Homeline Surgebreaker cUL _{US} Listed Secondary Surge Arrester 150 Vac line-to-ground maximum.	HOM2175SB	106.00	DE1B
Surge Arrester Mounting Kit:	UL Listed for mounting SDSA1175 surge arrester into ground bar mounting holes on 1Ø convertible main circuit breaker load centers	QOSAMK	7.60	DE3A
Replacement Cover Directory Label:	1 through 42 numbered universal replacement directory label for load center covers.	LSDL	.36	DE5
Circuit Identification Stickers:	Circuit identification stickers for use on cover directory labels to identify branch circuits.	PSDS	.50	DE5



1 LOAD CENTERS