

## SmartRack 12U Wall-Mount Open Frame Rack

MODEL NUMBER: SRWO12UHD



### Highlights

- Open frame with 2 post mounting, 19" Width, 18" Depth
- Threaded (12-24) mounting holes
- Heavy duty steel frame
- Easy assembly

### Package Includes

- (1) 3mm L-Shaped Hex Key
- (2) Top/Bottom Panel Frames
- (2) Vertical Mounting Rails
- (8) M5 Button Head Cap Screws
- (24) #12-24 Equipment Mounting Screws

### Description

Designed with provisions to integrate wall mounting, easy equipment access and cable management, SmartRack wall-mounted open frame cabinets are perfect for network equipment in IT environments with limited floor space. The 19" wide open frame rack is a heavy-duty, open frame rack designed for secure, high density servers and networking applications in IT environments.

### Features

- 2-post wall mounting...EIA 19" width
- Threaded (12-24) mounting holes
- Heavy duty steel construction with diagonal support straps
- Durable black textured powder coat finish
- Easy Assembly

## Specifications

PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	18
Installed Whole System Maximum Rack Depth (cm)	45.72
Rack Height (U Spaces)	12
Shipping Dimensions (hwd / in.)	4 x 22 x 23.8
Shipping Dimensions (hwd / cm)	10.16 x 55.88 x 60.45
Shipping Weight (lbs.)	15.4
Shipping Weight (kg)	6.98
Unit Dimensions (hwd / in.)	24.8 x 20.1 x 18.24



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Unit Dimensions (hwd / cm)	62.992 x 51.05 x 46.33
Unit Weight (lbs.)	14.3
Unit Weight (kg)	6.48
Unit Dimensions (cm)	EXTERNAL DIMENSIONS: 63 x 51 x 46.3(HWD)
Color	Black
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.718
Hinged (Swings Away from Wall Bracket)	No
<b>SPECIAL FEATURES</b>	
Seismic Rack	No
<b>CERTIFICATIONS</b>	
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	EIA-310-D, IEC 60297-3-100, DIN 41494, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>