

## USB 3.0 SuperSpeed Active Extension Repeater Cable (A M/F), 5M (16-ft.)

MODEL NUMBER: **U330-05M**



### Description

Tripp Lite's 16-ft. USB 3.0 active extension cable is a bus powered extension cable that can be used to increase the length of a device cable without the worry of signal loss and potential performance problems. Increase the extension distance to 33 ft. (10 m.) by connecting two U330-05M together. USB limits a cable's length to 16ft. Any length above 16 feet requires the use of an active cable such as this one. This cable has a signal booster built in. The cable must be plugged directly into a USB port (either on the PC or a hub). Use a standard 6' 10' or 15' USB 3.0 A-B cable to reach the desired distance. The U330-05M provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, an external power supply will be required. The U330-05M accepts a 5V, 2A power supply with a 3.5 x 1.35mm DC jack. The output plug on the power supply should have a positive tip and a negative sleeve.

### Features

- Extend a USB 3.0 signal 16 ft. (5 m.)
- Increase the extension distance to 33 ft. (10 m.) by connecting two U330-05M together
- Works together with standard USB 3.0 cables
- Provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, an external power supply will be required.
- Accepts a 5V, 2A power supply with a 3.5 x 1.35mm DC jack. The output plug on the power supply should have a positive tip and a negative sleeve.
- Backward compatible to previous USB generations

### Highlights

- Extend a USB 3.0 signal 16 ft. (5 m.)
- Increase the extension distance to 33 ft. (10 m.) by connecting two U330-05M together
- Supports USB 3.0 SuperSpeed data transfer rates up to 5Gbps

### System Requirements

- A USB 3.0 Computer port and USB 3.0 device are required to meet USB 3.0 speeds. A USB 2.0 port or device can be used, but you will be limited to the speeds of that port / device.
- The U330-05M provides up to 150mA of power to the connected device. If your device requires more than 150mA of power, an external power supply will be required. The U330-05M accepts a 5V, 2A power supply with a 3.5 x 1.35mm DC jack. The output plug on the power supply should have a positive tip and a negative sleeve.

### Package Includes

- 5 meter ( 16-ft ) USB3.0 Super Speed A/A Active Extension Cable (USB-A M/F)

## Specifications

OVERVIEW	
Cable Type	USB
OUTPUT	



USB Charging	No
<b>INPUT</b>	
Cable Length (ft.)	16
Cable Length (m)	5
<b>PHYSICAL</b>	
Color	Gray
<b>CONNECTIONS</b>	
Connector A	USB 3.0 A (MALE)
Connector B	USB 3.0 A (FEMALE)
<b>SPECIAL FEATURES</b>	
Chromebook Compatible	Yes
<b>CERTIFICATIONS</b>	
Certifications	RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>