

USB 3.0 SuperSpeed Active Extension Repeater Cable (A M/F), 10M (33-ft.)

MODEL NUMBER: **U330-10M**



Description

Tripp Lite's 33-ft. USB 3.0 active extension cable is a bus powered extension cable that can be used to increase the length of a device cable without the worry of signal loss and potential performance problems. Increase the extension distance to 66 ft. (20 m.) by connecting two U330-10M together. USB limits a cable's length to 16ft. Any length above 16 feet requires the use of an active cable such as this one. This cable has a signal booster built in. The cable must be plugged directly into a USB port (either on the PC or a hub). Use a standard 6' 10' or 15' USB 3.0 A-B cable to reach the desired distance. The U330-10M provides up to 120mA of power to the connected device. If your device requires more than 120mA of power, an external power supply will be required. The U330-10M accepts a 5V, 2A power supply with a 3.5 x 1.35mm DC jack. The output plug on the power supply should have a positive tip and a negative sleeve.

Features

- Extend a USB 3.0 signal 33 ft. (10 m.)
- Increase the extension distance to 66 ft. (20 m.) by connecting two U330-10M together
- Works together with standard USB 3.0 cables
- Provides up to 120mA of power to the connected device. If your device requires more than 120mA of power, an external power supply will be required.
- Accepts a 5V, 2A power supply with a 3.5 x 1.35mm DC jack. The output plug on the power supply should have a positive tip and a negative sleeve.
- Backward compatible to previous USB generations

Highlights

- Extend a USB 3.0 signal 33 ft. (10 m.)
- Increase the extension distance to 66 ft. (20 m.) by connecting two U330-10M together
- Supports USB 3.0 SuperSpeed data transfer rates up to 5Gbps

System Requirements

- A USB 3.0 Computer port and USB 3.0 device are required to meet USB 3.0 speeds. A USB 2.0 port or device can be used, but you will be limited to the speeds of that port / device.
- The U330-10M provides up to 120mA of power to the connected device. If your device requires more than 120mA of power, an external power supply will be required. The U330-10M accepts a 5V, 2A power supply with a 3.5 x 1.35mm DC jack. The output plug on the power supply should have a positive tip and a negative sleeve.

Package Includes

- 10 meter (33-ft) USB3.0 Super Speed A/A Active Extension Cable (USB-A M/F)

Specifications

OVERVIEW	
Cable Type	USB
OUTPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Charging	No
INPUT	
Cable Length (ft.)	33
Cable Length (m)	10
PHYSICAL	
Color	Gray
CONNECTIONS	
Connector A	USB 3.0 A (MALE)
Connector B	USB 3.0 A (FEMALE)
SPECIAL FEATURES	
Chromebook Compatible	Yes
CERTIFICATIONS	
Certifications	RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>