

## 3M™ Workstation Monitor Checker CTE701A

The Workstation Monitor Checker CTE701A is designed to verify proper operation of the 3M™ WS Aware Workstation Monitor, 3M™ Ground Master Equipment Ground Monitor, 3M™ Iron Man Plus Workstation Monitor, and 3M™ Ground Man Plus Ground Monitor. The Checker CTE701A simulates proper resistance, impedance and voltage signals so that you can see whether the response of your monitors complies with your specification.

Checker presents certain loads and signals to the monitor that simulate specific parameters of ground connections and wrist straps.



### Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive  
Sanford, NC 27332-9733  
Toll-Free: 866-722-3736  
International: 919-718-0000  
Email: 3mstaticinfo@mmm.com  
www.3Mstatic.com

Specifications	Typical Value
Dimensions	2.8 in. W x 5.0 in. L x 1.3 in. H (7.1 cm W x 12.7 cm L x 3.3 cm H)
Input Voltage	9VDC
Wrist Strap Resistance	10 megohms (default), 12 megohms (optional)
Metal Ground Impedance	10 ohms (default), 1-16 ohms (optional)
Soft Ground Resistance	10 megohms (default), 100, 400, 1,000megohms (optional)
EMI	Elevated threshold
Part Numbers	
CTE701A	Workstation Monitor Checker

3M is a trademark of 3M Company.

#### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

#### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**