

# 1-Port USB over Cat5/Cat6 Extender, Transmitter and Receiver, up to 150-ft.

MODEL NUMBER: **B202-150**



## Description

Tripp Lite's USB 1.1 over Cat5 Extender Kit allows you to connect your computer to a USB 1.1 peripheral up to 150 feet away using ordinary Cat5/Cat5e/Cat6 cable. The transmitter and receiver kit is bus-powered, so no external power supply is required. Plug-and-play; no software or drivers needed. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

## Features

- Locate a USB 1.1 peripheral up to 150 feet from your computer
- Bus Powered - no additional AC adapters required
- Uses readily available Cat5/Cat5e/Cat6 cable ( not included )
- Transfer rates of 1.5Mbps to 12Mbps
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

| OVERVIEW                    |                                     |
|-----------------------------|-------------------------------------|
| Cable Type                  | USB; UTP (Cat5, Cat5e, Cat6, Cat6a) |
| PHYSICAL                    |                                     |
| Color                       | Black                               |
| ENVIRONMENTAL               |                                     |
| Operating Temperature Range | 0 to 40 C (32 to 104 F)             |
| Storage Temperature Range   | -20 to 60 C (-4 to 140 F)           |

## Highlights

- Locate a USB 1.1 peripheral up to 150 feet from your computer
- Uses readily available Cat5/Cat6 cable
- Bus-powered; no external power supply required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Applications

- Use with USB 1.1 peripherals that need to exceed the 16 ft. (5 m.) distance limitation

## Package Includes

- Local transmitter unit
- Remote receiver unit
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

|                                     |                         |
|-------------------------------------|-------------------------|
| Relative Humidity                   | 20 to 90%               |
| <b>CONNECTIONS</b>                  |                         |
| Connector A                         | USB A (MALE)            |
| Connector B                         | RJ45 (FEMALE) (X2)      |
| Connector C                         | USB A (FEMALE)          |
| Ports                               | 1                       |
| <b>SPECIAL FEATURES</b>             |                         |
| Chromebook Compatible               | Yes                     |
| <b>WARRANTY</b>                     |                         |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>