

Component Video with Stereo Audio over Cat5/Cat6 Extender, Wallplate Remote Receiver

MODEL NUMBER: **B136-100-WP-1**



Description

The B136-100-WP-1 is a remote extender wallplate for the [B136-004](#), 4-Port Component Video + Audio Extender/Splitter. A 1080i(60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable([Tripp Lite N022-01K-GY](#)"> N022-01K-GY or [N222-01K-GY](#)"> N222-01K-GY); or, up to 400 ft. when using Zero-Skew UTP cable([Tripp Lite P524-01K](#)"> P524-01K). A 480p(60Hz) Component Video and Stereo Audio signal can be extended up to 500 ft. when using 24Awg, Solid Wire UTP cable([Tripp Lite N022-01K-GY](#) or [N222-01K-GY](#)); or, up to 700 ft. when using Zero-Skew UTP cable([Tripp Lite P524-01K](#)). No external power required.

Features

- Remote extender wallplate for the [B136-004](#) 4-port Extender/Splitter
- RJ45 Jack rear connector
- A 1080i(60Hz) Component Video and Stereo Audio signal can be extended up to 300 ft. when using 24Awg, Solid Wire UTP cable([Tripp Lite N022-01K-GY](#) or [N222-01K-GY](#)); or, up to 400 ft. when using Zero-Skew UTP cable([Tripp Lite P524-01K](#))
- No external power required

Specifications

OVERVIEW	
Display Style	Splitter
Cable Type	Component; UTP (Cat5, Cat5e, Cat6, Cat6a)
CONNECTIONS	
Connector A	HARDWIRE
Connector B	HARDWIRE

Highlights

- Remote extender wallplate for the [B136-004](#) 4-Port Extender/Splitter
- Extends a 1080i(60Hz) Component Video and Stereo Audio signal up to 300 ft. when using 24Awg, Solid Wire UTP cable
- Tripp Lite [N022-01K-GY](#) or [N222-01K-GY](#); or, up to 400 ft. when using Zero-Skew UTP cable([Tripp Lite P524-01K](#))
- RJ45 Jack rear connection
- No external power required

Package Includes

- B136-100-WP-1 Component Video + Stereo Audio Remote Extender Wallplate
- Wallplate Mounting Screws
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Ports	1
Side A - Connector 1	(x5) RCA Female
Side A - Connector 2	RJ45 Jack
SPECIAL FEATURES	
Chromebook Compatible	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>