

D26 Series — Type M, 600V AC Multipole with Convertible Contacts



4-Pole



4-Pole  
with Latch



4-Pole with Pneumatic  
Timer Attachment

Product Selection — Relays

When Ordering Specify

- Catalog Number and Magnet Coil Suffix Letter.
- Example: For a 4-pole relay having 4NO contacts, order Catalog Number **D26MR40**, with a 120V, 60 Hz coil, order **D26MR40A**.
- For fast delivery and minimum inventory, it is recommended that component parts or complete relays with NO poles be ordered.

Table 49-133. Complete AC Relays

Number of Contacts	Type of Contacts		Open Type				
	NO	NC	Relay Only		Relay with Mechanical Latch		
			Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	
2	2	0	D26MR20		D26MR202		
	1	1	D26MR11		D26MR112		
	0	2	D26MR02		D26MR022		
3	3	0	D26MR30		D26MR302		
	2	1	D26MR21		D26MR212		
	1	2	D26MR12		D26MR122		
4	0	3	D26MR03		D26MR032		
	4	0	D26MR40		D26MR402		
	3	1	D26MR31		D26MR312		
	2	2	D26MR22		D26MR222		
6	1	3	D26MR13		D26MR132		
	0	4	D26MR04		D26MR042		
	6	0	D26MR60		D26MR602		
	5	1	D26MR51		D26MR512		
8	4	2	D26MR42		D26MR422		
	3	3	D26MR33		D26MR332		
	2	4	D26MR24		D26MR242		
	1	5	D26MR15		D26MR152		
	0	6	D26MR06		D26MR062		
	8	0	D26MR80		D26MR802		
	7	1	D26MR71		D26MR712		
	6	2	D26MR62		D26MR622		
10 - 12	5	3	D26MR53		D26MR532		
	4	4	D26MR44		D26MR442		
	3	5	D26MR35		D26MR352		
	2	6	D26MR26		D26MR262		
	1	7	D26MR17		D26MR172		
	0	8	D26MR08		D26MR082		
	The 6 and 8 contact relays (without Mechanical Latch only) listed above can be provided with four additional NO non-convertible contacts. Add Suffix Number 4 to above listed Catalog Number plus Magnet Coil Suffix. Example: For a 12 contact relay, order D26MR804A.						

Relay with Pneumatic Timer Attachment Factory Installed (without Relay Contacts)

The relays listed below will accept up to four Catalog Number D26MPR contacts (convertible — NO or NC) for instantaneous operation. Order contacts separately. For additional information on timer attachment, see Page 49-89.

Table 49-134. Relay with Pneumatic Timer Attachment

Number of Available Instantaneous Contact Positions (Order Contacts Separately — Catalog Number D26MPR)	Timer Operation			
	ON Delay		OFF Delay	
	Catalog Number ①	Price U.S. \$	Catalog Number ①	Price U.S. \$
4	D26MR005		D26MR006	

① Consult Customer Support Center for availability.

For assembly of relays from component parts and relay accessories, see listing below.

Table 49-135. Magnet Coil Selection Table

Volts/Hertz	Suffix Number	Volts/Hertz	Suffix Number
120/60 – 110/50	A	32/60 ②	V
240/60 – 220/50	B	12/60 ②	R
208/60 ②	E	6/60	P
24/60	T	380/50 ②	L
277/60	H	480/60 or 440/50	C
		600/60 or 550/50 ②	D

② Consult Customer Support Center for availability.

Product Selection — Component Parts  
Separate Contacts



Front Pole

Rear Pole

Table 49-136. Separate Contacts

Description	Catalog Number	Price U.S. \$
<b>Convertible Contacts</b>		
Rear Pole – NO	D26MPR	
Rear Pole – NC	D26MPR02	
Front Pole – NO	D26MPF	
Front Pole – NC	D26MPF02	
Gold Plated (for low power circuits)		
Rear Pole – NO	D26MPR03	
Front Pole – NO	D26MPF03	
<b>Non-convertible Contacts</b>		
Rear Pole NO Early Closing ③	D26MPS	
Rear Pole NC Late Opening ③	D26MPL	

③ To obtain overlapping contacts, these two special poles must be used in related circuits.