

## General Information

<b>Kit Part Number:</b>	<a href="#">76650-0051</a>
<b>Description:</b>	PVC Insulated Bullet Snap Plug and Receptacle, and Non-Insulated Bullet Snap Plug and Receptacle
<b>Application:</b>	Automotive / Transportation, MRO (Maintenance Repair and Operations)
<b>Connector Family:</b>	Snap Bullet
<b>Solution:</b>	Maintenance, Repair and Operation Connectors
<b>Connector Type:</b>	Solderless Terminals
<b>Number of Pieces:</b>	150
<b>RoHS:</b>	Yes

## Specifications

<b>Insulation:</b>	PVC, Non-Insulated
<b>Insulation Type:</b>	PVC, Non-Insulated
<b>Mounting Style:</b>	Non-Mounted
<b>Orientation:</b>	Solderless Terminals
<b>Product/Type:</b>	Bullet Snap Plugs
<b>Stud/Tab Size:</b>	.156" (3.96mm)
<b>Tool Included:</b>	No
<b>Wire Gauge (AWG):</b>	16-14 , 22-18

## Product Highlights

### Product Highlights

Snap Solderless Terminals are easier and quicker to connect / mate. These are suitable for blind / hidden mating applications. These do not have to mate planarily like Quick Connects, but radially 360 deg.

### Features and Benefits

- Can be connected and disconnected repeatedly
- Designed to SAE specifications
- Features a PVC sleeve to protect against vibration damage by preventing wire flex at the crimp point
- Funnel entrance into the electrical barrel (on insulated) eliminates wire strand fold back and increases crimping rate

### Applications

- MRO (Maintenance Repair and Operations)
- Automotive

**Bill of Materials**

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
<a href="#">19033-0003</a>	25	3.96mm (.156") Non-insulated, Male Snap Bullet Connector, 22...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">19033-0007</a>	25	3.96mm (.156") Non-insulated, Male Snap Bullet Connector, 16...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">19034-0005</a>	25	3.96mm (.156") PVC, Male Snap Bullet Connector, 22-18 AWG	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">19034-0009</a>	25	3.96mm (.156") PVC, Male Snap Bullet Connector, 16-14 AWG	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">19038-0001</a>	25	3.96mm (.156") PVC, Female Snap Bullet Connector, 22-18 AWG	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">19038-0007</a>	25	3.96mm (.156") PVC, Female Snap Bullet Connector, 16-14 AWG	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>

**Recommended Tool**

Part No.	Included in Kit
<a href="#">64001-0100</a>	No
<a href="#">64001-0300</a>	No
<a href="#">64003-0100</a>	No
<a href="#">64001-1400</a>	No
<a href="#">64001-5900</a>	No
<a href="#">64005-5900</a>	No





