

Power plug - BL2-2,54/16-ST - 2896335


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Power connector for DIN rail bus connector with 16 free cable ends with a cross section of 0.25 mm², 500 mm long, female contacts



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| GTIN |  4 046356 098410 |
| Weight per Piece (excluding packing) | 36.69 g |
| Custom tariff number | 85369010 |
| Country of origin | Taiwan |
| Product key | ACHBBZ |
| Note | Made to Order (non-returnable) |

Technical data

General

| | |
|------------------|-------------------|
| Housing type | Component housing |
| Housing material | Polyamide |

Technical data

| | |
|----------------------------------|------|
| Connection in acc. with standard | CUL |
| Nominal voltage U _N | 60 V |
| Nominal current I _N | 2 A |
| Indicator1 | CUL1 |

Standards and Regulations

| | |
|----------------------------------|-----|
| Connection in acc. with standard | CUL |
|----------------------------------|-----|

Power plug - BL2-2,54/16-ST - 2896335

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440309 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002638 |
| ETIM 5.0 | EC002638 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11 | 39121409 |
| UNSPSC 12.01 | 39121409 |
| UNSPSC 13.2 | 39121409 |

Approvals

Approvals


Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

| | |
|---|------|
| UL Recognized  | |
| Nominal current IN | 2 A |
| Nominal voltage UN | 60 V |

Power plug - BL2-2,54/16-ST - 2896335

Approvals

| | |
|--------------------|------|
| cUL Recognized | |
| Nominal current IN | 2 A |
| Nominal voltage UN | 60 V |

EAC

cULus Recognized

Drawings

Circuit diagram

