

PROLINE G2 SIDE DOOR ADAPTER

APPLICATION

PROLINE G2 Side Door Adapters allow the mounting of a standard door to the side of the enclosure. When mounted to the enclosure, they maintain enclosure environmental integrity.

SPECIFICATIONS

- 14 gauge (1.75 mm) steel
- All mounting hardware included
- EMC Barrier Panels are plated to provide corrosion resistance while maintaining a metal-to-metal contact

FINISH

- Polyester powder paint; RAL 7035 textured light gray standard
- Dip coated primed
- Custom colors available

BULLETIN: P40

Standard Product

Catalog Number	Description
P2DA64	Fits frames 600-mm tall x 400-mm deep
P2DA66	Fits frames 600-mm tall x 600-mm deep
P2DA68	Fits frames 600-mm tall x 800-mm deep
P2DA86	Fits frames 800-mm tall x 600-mm deep
P2DA88	Fits frames 800-mm tall x 800-mm deep
P2DA105	Fits frames 1000-mm tall x 500-mm deep
P2DA106	Fits frames 1000-mm tall x 600-mm deep
P2DA108	Fits frames 1000-mm tall x 800-mm deep
P2DA125	Fits frames 1200-mm tall x 500-mm deep
P2DA126	Fits frames 1200-mm tall x 600-mm deep
P2DA128	Fits frames 1200-mm tall x 800-mm deep
P2DA145	Fits frames 1400-mm tall x 500-mm deep
P2DA148	Fits frames 1400-mm tall x 800-mm deep
P2DA164	Fits frames 1600-mm tall x 400-mm deep
P2DA165	Fits frames 1600-mm tall x 500-mm deep
P2DA166	Fits frames 1600-mm tall x 600-mm deep
P2DA168	Fits frames 1600-mm tall x 800-mm deep
P2DA184	Fits frames 1800-mm tall x 400-mm deep
P2DA185	Fits frames 1800-mm tall x 500-mm deep
P2DA186	Fits frames 1800-mm tall x 600-mm deep
P2DA188	Fits frames 1800-mm tall x 800-mm deep
P2DA204	Fits frames 2000-mm tall x 400-mm deep
P2DA205	Fits frames 2000-mm tall x 500-mm deep
P2DA206	Fits frames 2000-mm tall x 600-mm deep
P2DA208	Fits frames 2000-mm tall x 800-mm deep
P2DA210	Fits frames 2000-mm tall x 1000-mm deep
P2DA225	Fits frames 2200-mm tall x 500-mm deep
P2DA226	Fits frames 2200-mm tall x 600-mm deep
P2DA228	Fits frames 2200-mm tall x 800-mm deep
P2DA2210	Fits frames 2200-mm tall x 1000-mm deep
P2DA146HF	Fits EMC frames 1400-mm tall x 600-mm deep
P2DA186HF	Fits EMC frames 1800-mm tall x 600-mm deep
P2DA206HF	Fits EMC frames 2000-mm tall x 600-mm deep
P2DA226HF	Fits EMC frames 2200-mm tall x 600-mm deep

Model	Component	Type	Height	Depth	Specialty	Catalog Number
P2	D	A	20	6	Blank	= P2DA206
PROLINE G2	Door	Blank = single door O = double door W = window door A = side door adapter DR = disconnect right DL = disconnect left DR2 = disconnect right large cutout F = dress frame	mm 22 = 2200 20 = 2000 18 = 1800 16 = 1600 14 = 1400 12 = 1200 10 = 1000 8 = 800 6 = 600	mm 10 = 1000 8 = 800 6 = 600 5 = 500 4 = 400	Blank = standard HF = EMC protected	

Notes