

4-Post Rack-Mount Installation Kit for Select Rack-Mount UPS Systems, Side Mount

MODEL NUMBER: 4POSTRAILSM



Highlights

- Supports UPS systems in EIA-standard 4-post racks
- Supports up to 250 lb.
- Compatible with mounting depths of 16.5–21.5 in.
- Leaves front and rear mounting holes free for equipment
- Includes rack-attachment hardware for square-hole mounting

Package Includes

- (2) L brackets
- (8) M6 screws
- (8) M6 cup washers
- (8) M6 cage nuts

Description

The 4POSTRAILSM 4-Post Rack-Mount Installation Kit supports heavy UPS systems in your EIA-standard four-post rack. The two L brackets mount to the outside edges of the rack's vertical mounting rails – the edges facing the side panels – using the rails' square mounting holes. Attaching the 4POSTRAILSM to the side leaves your front and rear mounting holes free for equipment.

The brackets support up to 250 pounds and are compatible with four-post racks with a mounting depth of 16.5 to 21.5 inches. In addition to UPS systems, the 4POSTRAILSM is compatible with other heavy networking or power protection equipment with a rectangular chassis of 17.5 inches in width. Rack-attachment hardware for square-hole mounting is included.

Features

Extra Support for Heavy UPS Systems

- Installs on outside edges of rack's vertical mounting rails
- Compatible with EIA-standard 4-post racks with mounting depths of 16.5–21.5 in.
- Leaves front and rear mounting holes free for equipment
- Supports up to 250 lb.
- Also supports other heavy networking or power protection equipment 17.5 in. wide
- Rack-attachment hardware for square-hole mounting included

Specifications

OVERVIEW	
Accessories Type	Rackmount Kit
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / in.)	6.3 x 5.71 x 25.4
Shipping Dimensions (hwd / cm)	16 x 14.5 x 64.5
Shipping Weight (lbs.)	4.2
Shipping Weight (kg)	1.91
Weight Capacity - Stationary (lbs.)	250
Weight Capacity - Stationary (kg)	112.50
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2016 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>