

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0449150001](#)
Status: **Active**
Overview: [Modular Jacks and Plugs](#)
Description: [Modular Plug, Category 6, Long Body, Unshielded, 8/8](#)

Documents:

3D Model	Packaging Specification PK-44915-003 (PDF)
Drawing (PDF)	Packaging Specification PK-44915-004 (PDF)
Product Specification PS-44915-003-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL E107635

General

Product Family	Modular Jacks/Plugs
Series	44915
Component Type	Wire Plug
Magnetic	No
Overview	Modular Jacks and Plugs
Performance Category	6
Power over Ethernet (PoE)	N/A
Product Name	RJ45
UPC	800756394305

Physical

Color - Resin	Clear
Durability (mating cycles max)	500
Inverted / Top Latch	N/A
Jack Height	N/A
Lightpipes/LEDs	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polycarbonate
Net Weight	1.504/g
Orientation	N/A
PCB Locator	No
PCB Retention	None
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	1.02mm
Pitch - Termination Interface	1.27mm
Ports	1
Positions / Loaded Contacts	8/8
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	N/A
Wire/Cable Type	Round


Electrical

Current - Maximum per Contact	1.5A
Grounding to Panel	N/A
Shielded	No
Voltage - Maximum	125V

Solder Process Data

Lead-freeProcess Capability N/A

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[44915 Series](#)

Mates With

FCC 68 Jacks

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

PK-44915-003, PK-44915-004

PS-44915-003-001

SD-44915-001, SD-44915-002

This document was generated on 01/04/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION