

General Information

Extended Product Type:	BAZ1
Product ID:	1SNK900002R0000
EAN:	3472599163737
Catalog Description:	BAZ1 End Stops - Dark Grey
Long Description:	- Reduce the size of your terminal block assemblies with the screwless reduced spacing BAZ1 end stop, - Ease the assemblies identification with various markers and label holders.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » End Stops

Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010
Color:	Dark Grey

Dimensions

Product Net Height:	54.4 mm
Product Net Length:	34.2 mm
Product Net Depth:	34.2 mm
Product Net Weight:	5.3 g
Product Net Width:	5.2 mm

Technical

Spacing:	5.2 mm
Connection Type:	Spring
Function:	End Stops
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Suitable For:	ZDK2.5-22 ZDK4-22 ZDP2.5-11 ZDP2.5-22 ZDP2.5-D1 ZDP2.5-D2 ZDS4-22 ZDS4-22-R1 ZK10 ZK10-3P ZK10-PE ZK10-PE-3P ZK16 ZK16-3P ZK16-PE ZK16-PE-3P ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-CH-4P ZK2.5-PE ZK2.5-PE-3P ZK2.5-PE-4P ZK2.5-S ZK2.5-S-4P ZK2.5-SF ZK2.5-SF-R ZK2.5-SP ZK2.5-SP-4P ZK2.5-S-R1 ZK4 ZK4-3P ZK4-4P ZK4-PE ZK4-PE-3P ZK4-PE-4P ZK6 ZK6-3P

ZK6-PE
ZK6-PE-3P
ZP2.5
ZP2.5-3P
ZP2.5-4P
ZP2.5-D1
ZP2.5-D2
ZP2.5-PE
ZP2.5-PE-3P
ZP2.5-PE-4P
ZP2.5-S
ZP2.5-SP
ZS10
ZS10-PE
ZS10-PE-R1
ZS10-R1
ZS10-S
ZS10-SF
ZS10-SF-R
ZS10-SP
ZS10-S-R2
ZS10-ST
ZS10-ST-1
ZS10-ST-T4
ZS16
ZS16-PE
ZS25
ZS25-PE
ZS4
ZS4-PE
ZS4-PE-R2
ZS4-R1
ZS4-R2
ZS4-S
ZS4-SF
ZS4-SF1
ZS4-SF1-R
ZS4-SF1-T
ZS4-SF-R
ZS4-SF-T
ZS4-SP
ZS4-SP-R1
ZS4-SP-T2
ZS4-SP-T2-R1
ZS4-S-R1
ZS4-S-R2
ZS4-S-R3
ZS4-S-T
ZS4-S-T-R1
ZS6
ZS6-3S
ZS6-3S-PE
ZS6-4S
ZS6-4S-PE
ZS6-PE
ZS6-S
ZS6-S-4S-T

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2011/65/EC

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230479F0206

Classifications

E-nummer: 2925147

ETIM 4: EC001041 - End bracket for terminal block

ETIM 5: EC001041 - End bracket for terminal block

ETIM 6: EC001041 - End bracket for terminal block

Object Classification Code: X

Container Information

Package Level 1 Width:	200 mm
Package Level 1 Length:	300 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.265 kg
Package Level 1 EAN:	3472599163737
Package Level 2 Units:	750 piece
Package Level 2 Width:	300 mm
Package Level 2 Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 3 Units:	36000 piece
Product Packing Type:	Bag
Package Level 1 Units:	50 piece

