

General Information

Extended Product Type:	JB85-3
Product ID:	1SNK900603R0000
EAN:	3472599163683
Catalog Description:	JB85-3 Cross Spacing Jumper - Orange
Long Description:	- Allows power distribution between terminal blocks with different spacing, - JB5-3, JB6-3 and JB8-3 can be used as cross spacing jumpers (see selection table on Mounting instructions below).

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Cross Spacing Jumpers

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010
Color:	Orange

Dimensions

Product Net Height:	27.8 mm
Product Net Length:	42.5 mm
Product Net Depth:	42.5 mm
Product Net Weight:	2.8 g
Product Net Width:	8 mm

Technical

Spacing:	8 mm
Function:	Cross Spacing Jumpers
Rated Current (I_n):	Main Circuit 32 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 480 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	0.1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZDK2.5-22 ZDK4-22 ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-PE ZK2.5-PE-3P ZK2.5-PE-4P ZK2.5-S ZK2.5-SF ZK2.5-SF-R ZK2.5-SP ZK2.5-S-R1 ZK4 ZK4-3P ZK4-4P ZK4-PE ZK4-PE-3P ZK4-PE-4P ZK6 ZK6-3P ZK6-PE ZK6-PE-3P ZS10 ZS16 ZS16-PE ZS25 ZS25-PE

ZS4
ZS4-PE-R2
ZS4-R2
ZS4-SF
ZS4-SF-R
ZS4-SF-T
ZS4-SP-R1
ZS4-SP-T2-R1
ZS4-S-R1
ZS4-S-R2
ZS4-S-T-R1
ZS6
ZS6-3S
ZS6-3S-PE
ZS6-4S
ZS6-4S-PE
ZS6-PE
ZS6-S-4S-T

Technical UL/CSA

Flammability According to UL94: V0
Maximum Operating Voltage UL/CSA: Main Circuit 600 V

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant
RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201
Data Sheet, Technical Information: 1SNK160035D0201
RoHS Information: 1SND230508F0202

Classifications

E-nummer: 2925162
ETIM 4: EC000489 - Cross-connector for terminal block
ETIM 5: EC000489 - Cross-connector for terminal block
ETIM 6: EC000489 - Cross-connector for terminal block
Object Classification Code: X

Container Information

Package Level 1 Width: 50 mm
Package Level 1 Length: 117 mm
Package Level 1 Height: 50 mm
Package Level 1 Gross Weight: 0.028 kg
Package Level 1 EAN: 3472599163683
Package Level 2 Units: 300 piece
Package Level 3 Units: 28800 piece
Package Level 1 Units: 10 piece

