

## Industrial Keyboard Covers Clear and Flexible



### Main Applications

- HealthCare – easily disinfected & latex free
- Government/Military – durable construction
- Retail – POS compatible
- Consumer – 24/7 protection
- Industrial applications – Chemical resistant

### Key Features

- Remains securely in place during use
- Protects against liquid spills, food, oil, dampness and dirt
- Flexible, transparent, durable
- Easily cleaned/disinfected in place
- Works with touchpad & card reader keyboards
- Custom made for a perfect fit

### Main Part Numbers

- **KBCV0800W**  
Plastic keyboard cover for all US layout JK-0800 models.
- **KBCV11900W**  
Plastic keyboard cover for all US layout G80-11900 models.
- **KBCV1800N**  
Plastic keyboard cover for all US layout G8x-1800 models without 'Windows keys'.
- **KBCV1800W**  
Plastic keyboard cover for all US layout G8x-1800 models with 'Windows keys'.
- **KBCV4100N**  
Plastic keyboard cover for all G84-4100 models without 'Windows keys'.
- **KBCV4100W**  
Plastic keyboard cover for all G84-4100 models with 'Windows keys'.
- **KBCV4400**  
Plastic keyboard cover for all US layout G84-4400 models.
- **KBCV6100W**  
Plastic keyboard cover for all G83-6104 models with 'Windows keys'.
- **KBCV23200W**  
Plastic keyboard cover for all US English G85-23x00 models with 'Windows keys'.
- **KBCV61401W**  
Plastic keyboard cover for all G86-61401 models.
- **KBCV61411W**  
Plastic keyboard cover for all G86-61411 models.
- **KBCV62401W**  
Plastic keyboard cover for all standard G86-62401 models.
- **KBCV62410W**  
Plastic keyboard cover for all G86-62410 models.
- **KBCV62411W**  
Plastic keyboard cover for all G86-62411 models.
- **KBCV6700W**  
Plastic keyboard cover for all G83-67xx models.
- **KBCV7000W**  
Plastic keyboard cover for all G81-7000 models with 2 & 3 track magnetic stripe reader.
- **KBCV8000W**  
Plastic keyboard cover for all G81-8000 models with 2 & 3 track magnetic stripe reader.

## Industrial Keyboard Covers Clear and Flexible



### Technical Data

#### Material

100% polyurethane w/ UV inhibitor

#### Maximum Service temperature

°F -60° to 200°

°C -53° to 93°

#### Thickness

10.5 mil

### Easy Installation



- Gently lay cover over keyboard and align cover with the keys.



- Remove white backing from adhesive strips.



- Apply pressure to adhesive edge while smoothing out the cover.

### Contact

Call or visit our website for more information.

#### Cherry Americas, LLC

11200 88th Avenue

Pleasant Prairie, WI 53158 USA

Phone: 262.942.6508

Internet: [www.cherryamericas.com](http://www.cherryamericas.com)

E-Mail:

[keyboardsupport@cherryamericas.com](mailto:keyboardsupport@cherryamericas.com)

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.