

## TAA-Compliant External 48V 3U Battery Pack for select Tripp Lite UPS systems (BP48V60RT3UTAA-Compliant)

MODEL NUMBER: BP48V60RT3UTAA



### Description

BP48V60RT3UTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. Rack/tower external battery pack offers extended battery runtime when used in conjunction with expandable 48V Tripp Lite rackmount and tower UPS systems. Includes heavy gauge cabling with high current DC connector for safe, simple installation. Included daisychain connector enables the connection of additional compatible 48V external battery packs to the host UPS. Included mounting accessories support 3U rackmount installation in 4 post racks. Options for 2 post center-mounting and upright tower installation available.

Compatible with these UPS Systems - [SM2200RMDVTAA](#), [BP48V60RT3UTAA](#), [SMART1500CRMXL](#), [SMART2200CRMXL](#), [SMART2200RMXL2U](#), [SMART2200RMXL2UP](#), [SMART2200RMXLN](#), [SMART2200VSXL](#), [SMART2600RM2U](#), [SMART3000CRMXL](#), [SMART3000RM2U](#), [SMART3000RM2UN](#), [SMART3000RMXL2U](#), [SMART3000RMXLN](#), [SMART3000VS](#), [SMART5000RT3U](#), [SMART5000XFMXL](#), [SMARTINT3000VS](#), [SMX2200XLRT2U](#), [SMX3000XLRT2UA](#), [SMX5000XLRT3U](#), [SU1500RTL2UA](#), [SU1500RTLXCD2U](#), [SU1500XL](#), [SU1500XLCD](#), [SU2200RTL2UA](#), [SU2200RTLXCD2U](#), [SU2200XLA](#), [SU2200XLCD](#), [SUINT2200RTL2UA](#) and other Tripp Lite UPS systems that specify the use of this battery pack.

### Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Offers extended-run UPS operation when used in conjunction with compatible 48V DC Tripp Lite UPS systems
- Includes heavy gauge cabling with high current DC connectors for simple installation
- Daisychain connector enables the connection of additional compatible 48V external battery packs to the host UPS
- Included mounting brackets support rackmount installation in 4 post racks using only 3 rack spaces (3U)
- [2POSTRMKITHD](#) option supports balanced 2 point center-mounting in 2 post equipment racks
- [2-9USTAND](#) option enables upright tower placement

## Specifications

### Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- Extends the runtime of expandable 48V DC Tripp Lite UPS Systems
- Included daisychain connector supports the addition of multiple compatible external battery packs
- Supports 3U rackmount installation; 4 post installation accessories included
- Options for 2 post rackmount and tower installation available

### Package Includes

- BP48V60RT3UTAA TAA Compliant external battery pack with attached DC cabling
- 4 post compatible mounting hardware
- Owner's manual



<b>BATTERY</b>	
Expandable Battery Runtime	Blue 175 amp female connector for additional battery packs
DC System Voltage (VDC)	48
UPS Connection	20 inch attached cable with blue 175 amp male DC connector
Typical Battery Lifespan	4-6 years typical (North America)
Expandable Runtime	Yes
<b>PHYSICAL</b>	
Minimum Required Rack Depth (inches)	32
Minimum Required Rack Depth (cm)	81.28
Shipping Dimensions (hwd / in.)	11.25 x 23 x 31.5
Shipping Dimensions (hwd / cm)	28.6 x 58.4 x 80
Shipping Weight (lbs.)	200.6
Shipping Weight (kg)	91.1
Unit Dimensions (hwd / in.)	5.25 x 17.5 x 25
Unit Dimensions (hwd / cm)	13.3 x 44.4 x 63.5
Unit Weight (lbs.)	163.1
Unit Weight (kg)	73.98
Material of Construction	Steel
External Battery Pack Form Factor	Rack/Tower
Minimum Required Rack Depth (mm)	813
<b>ENVIRONMENTAL</b>	
Operating Temperature	32-104 degrees F / 0-40 degrees C
<b>CERTIFICATIONS</b>	
Certifications	TAA Compliant
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Puerto Rico)	1-year limited warranty
---------------------------------------	-------------------------

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>