



Vortex™ and Vortex™ 360° Duster

High Velocity Dusters

1697

Introduction

Formulated with HFC-134a, these exceptionally pure, moisture free, inert gas, high velocity products remove particles without the use of harmful solvents. Vortex™ 360°, an invertible high velocity duster, can be sprayed in any direction without threat of dispensing liquid on valuable equipment. Vortex™ and Vortex™ 360° clean and remove microscopic contaminants and dust particles from all types of electronic equipment. They are ideal for the removal of dust, lint and other contaminants from computers, printers as well as optical cleaning equipment.

Features / Benefits

- Non-Flammable
- Non-Ozone Depleting
- Leaves No Residue
- Quad-Filtered
- Inert
- Moisture Free

Chemical Components

1,1,1,2-Tetrafluoroethane.....	(811-97-2)	100%
--------------------------------	------------	------

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

Vortex™ and Vortex™ 360° are available in the following sizes:

1697-8S	8 Ounce Aerosol Invertible Duster
1697-10S	10 Ounce Aerosol

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Tech Spray L.P.
 P.O. Box 949
 Amarillo, TX 79105
 800-858-4043
 email: tsales@techspray.com

Europe

Techspray International
 UNIT 4, 44/46 Bunyan Road, Kempston
 Bedford MK42 8HL United Kingdom
 +44 (0) 1234 855443
 email: tseurope@techspray.com

Countries Outside US

Call to locate a distributor
 in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.
 P.O. Box 949
 Amarillo, TX 79105
www.techspray.com

[English MSDS](#)
[French MSDS](#)
[German MSDS](#)
[Italian MSDS](#)
[Spanish MSDS](#)

