

## DeoxIT® Fader FN5 Mini-Spray, F-Series Moving Contact Lubricant for Conductive Plastic Faders & Controls

**Part No.:** FN5MS-H15

**Container Size:** 14 g

### Product Description:

Precision lubricant for conductive plastics and carbon-based controls (faders, slide potentiometers, conductive membranes - mouse pads and other mechanisms with sliding surfaces). It replenishes lubrication lost on surfaces that have been cleaned with solvents or other cleaning solutions. Use on conductive plastics and other sliding metal-plastic surfaces. Temperature range: -26 to +150°C.



### Features/Benefits:

**Spray - Quick Dry, Non Drip and Safe on Plastics.**

DeoxIT® Fader F100L concentrate has approximately 0.0% chemical cleaning action. DeoxIT® Fader is not for metal contacts/connectors, use DeoxIT®, DeoxIT® GOLD and DeoxIT® SHIELD for those surfaces.

Replaces lubrication lost that have been cleaned with solvents or other cleaning solutions. Perfect for OEM's

Excellent enhancing, excellent protection, No ozone depletion. Reduces intermittent connections, arcing, RFI, wear and abrasion. **Cleaner Audio - Clearer Video - Reliable Data.**



### Formulation:

5%	DeoxIT® Fader F100L (formerly FaderLube/CaiLube MCL)
70-74%	1,1,1,3,3-PENTAFLUOROPROPANE (460-73-1)
1-5%	isopropyl alcohol (67-63-1)
20%	hydrocarbon propellant (75-28-5, 74-98-6)

### Other Applicators:

F5S-H6	5%	spray	142 g	flammable
F100S-L2	100%	spray	57 g	nonflammable
F100L-L2C	100%	squeeze tube	2 mL	nonflammable
F100L-L25C	100%	needle dispenser	25 mL	nonflammable
F100L (bulk)	100%	bottle/drum	assort.	nonflammable
F5L (bulk)	5%	bottle/drum	assort.	flammable

## **DeoxIT® Essential Reference:**

---

**DeoxIT®** - *Brings old systems back to life!*

**DeoxIT® GOLD** - *Maintains new system performance!*

**DeoxIT® SHIELD** - *Maintains new system performance for severe environments!*

## **Shipping Information:**

---

Hazardous: Y - ORMD

## **Other Information:**

---

RoHS Compliant:	YES
FN5MS-H15 MSDS Link:	<a href="http://store.caig.com/">http://store.caig.com/</a>
DeoxIT® Fader Product Sheet:	<a href="http://store.caig.com/">http://store.caig.com/</a>
MentorCard Link:	<a href="http://store.caig.com/">http://store.caig.com/</a>

## **MANUFACTURER DISCLAIMER:**

---

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.

## **Contact Information:**



### **North America**

CAIG Laboratories, Inc.  
12200 Thatcher Court  
Poway, CA 92064 USA  
Tel: (858) 486-8388  
Fax: (858) 486-8398

### **Website**

[www.caig.com](http://www.caig.com)  
[www.deoxit.com](http://www.deoxit.com)

### **General email**

[info@caig.com](mailto:info@caig.com)

### **Technical email**

[tech@caig.com](mailto:tech@caig.com)