



Datenblatt - Fiche technique - Data sheet


**21.15.2947**



ROLINE Patchkabel Kat.6 UTP, Component Level, LSOH, orange, 0,3 m

Cordon ROLINE UTP Cat.6, LSOH, Component Level, orange, 0,3 m

ROLINE UTP Cable Cat.6 Component Level, LSOH, orange, 0.3 m



**1. ELECTRICAL TEST:**

- (1). 100% OPEN SHORT & MISS WIRE TEST;
- (2). INSULATION RESISTANCE:DC 250V 20M OHM MIN;
- (3). CONTACTOR RESISTANCE:30 OHM MAX

2. PRINTING:GHMT® roline CAT.6 U/UTP COMPONENT PATCH CORD LSZH 250MHz ISO/IEC 11801 & EN 50173-1 & ANSI/TIA-568-C.2

3. 100% Component Patch cord Test PASS

4. Minimum bending radius:50mm

**MATERIAL LIST**

|     |                  |   |       |        |
|-----|------------------|---|-------|--------|
| ⑥   | LABEL            | NO DRY GLUE LABEL   | 1PCS  |        |
| ⑤   | MINI TIE         | PE MINI TIE (POSSESS METAL)                                     | 2PCS  |        |
| ④   | POLYETHYLENE BAG | POLYETHYLENE BAG  | 1PCS  |        |
| ③   | OVER MOLD        | 88A PVC Orange  | 2PCS  |        |
| ②   | CONNECTOR        | RJ45 8P8C' S UNSHIELDED PIN GOLD PLATED 3u", Transparent RED    | 2PCS  |        |
| ①   | CABLE            | U/UTP CAT.6 24AWG (BC*1P)*4+CROSS + JACKET LSOH<br>OD=6.0±0.2MM | 1PCS  |        |
| NO. | PARTS NAME       | SPECIFICATION STANDARD  | QT' Y | REMARK |

COLOUR:Orange (PANTONE:1575C)

| ITEM NO.     | LENGTH (L) | TOLERANCE (T) |
|--------------|------------|---------------|
| 21. 15. 2947 | 300mm      | ±10mm         |
| 21. 15. 2570 | 500mm      | ±15mm         |
| 21. 15. 2571 | 1000mm     | ±30mm         |
| 21. 15. 2574 | 1500mm     | ±45mm         |
| 21. 15. 2572 | 2000mm     | ±60mm         |
| 21. 15. 2573 | 3000mm     | ±90mm         |
| 21. 15. 2575 | 5000mm     | ±150mm        |
| 21. 15. 2576 | 7500mm     | ±210mm        |
| 21. 15. 2577 | 10000mm    | ±300mm        |
| 21. 15. 2578 | 15000mm    | ±450mm        |
| 21. 15. 2579 | 20000mm    | ±600mm        |

|              |  |              |              |              |              |
|--------------|--|--------------|--------------|--------------|--------------|
| ITEM NO.     | 21. 15. 2947   | 21. 15. 2570 | 21. 15. 2571 | 21. 15. 2572 | 21. 15. 2573 |
| 21. 15. 2574 | 21. 15. 2575   | 21. 15. 2576 | 21. 15. 2577 | 21. 15. 2578 | 21. 15. 2579 |
| DESC.        | ROLINE UTP PatchCord CAT. 6, LSOH, Comp. Level, Orange |              |              |              |              |

|    |     |                               |      |            |
|----|-----|-------------------------------|------|------------|
|    |     |                               |      |            |
|    |     | NEW                           |      | 2016-10-20 |
| BY | CHK | REVISION RECORD MODIFICATIONS |      | A          |
|    |     |                               | DATE | REV.       |

SECOMP