

GUD3C02

USB-C Ultra-Slim Docking Station with Power Delivery Pass-Thru




- Stylish and ultra slim docking station
- Supports versatile video options: HDMI (4K), Mini DisplayPort (4K) and VGA
- Get the most bang for your buck
- Charge your laptop while docked - Power Delivery Pass Through
- Instantly dock up to 10 devices, including built-in memory card readers

Turn Your Laptop into a Complete Workstation

Add the perfect companion to your USB-C laptop and turn it into a complete workstation. Whether you are on-the-go or docking at a workstation, this ultra-slim docking station works as hard as you do. With it's stylish design, it will seamlessly fit into your setup. Now you can easily add a full-sized keyboard and mouse, external hard drives, printers, webcams by connecting only one cable to your setup.

- Stylish and ultra slim docking station
 - Instantly dock up to 10 devices including
 - 3 x USB 3.0 (USB Type-A) with 1 x BC 1.2 Quick Charge Port
 - Built-in memory card readers (SD/MMC/Micro SD)
 - 3.5mm audio input/output
 - Gigabit Ethernet
 - HDMI (4K), Mini DisplayPort (4K) and VGA
 - Charge your laptop while docked- Power Delivery pass-through*
 - Stunning 4K resolution
- * Power Delivery pass-through requires USB-C charger from your laptop. A total of up to 60W can be charged to the laptop after deduction of 15W is used by the dock.
- ** When using the HDMI/VGA ports, only one video output is supported at a time (either VGA or HDMI)
- ** When using the MiniDP/VGA ports, only one video output is supported at a time (either VGA or MiniDP)





Requirements

Package Contents

- | | |
|---|---|
| <ul style="list-style-type: none"> • USB-C compatible laptops with DP Alt-Mode support • USB-C AC Adapter from Laptop is needed for Power Delivery Pass-Thru Function • Mac OS X 10.10.5+ (*MST is not supported by Mac OS) • Only one additional video output can be utilized for extended desktop using Mac OS • For dual screen extended desktop in Windows, you must use HDMI with Mini Display Port • When VGA output is utilized, only one additional extended desktop screen will be available • Compatible with USB-C and Thunderbolt 3 laptop | <ul style="list-style-type: none"> • 1 x USB-C Docking Station • 1 x Quick Start Guide • 1 x Warranty Card |
|---|---|

Specifications

Function	GUD3C02	Dimensions	GUD3C02
Upstream Port		Unit Dimensions	
USB-C	Built-in USB 3.1 Type-C cable	Height	0.6" (1.52cm)
Cable Length		Depth	3.0" (7.62cm)
		Length	11" (27.94cm)
Downstream Port		Unit Package Dimensions	
Audio In	3.5 mm line-in	Width	13.5" (34.29cm)
Audio Out	3.5 mm line-out	Height	4.5" (11.43cm)
HDMI	1x HDMI port (v.1.4 spec compliant, up to 3840x2160@30Hz)	Depth	1.4" (3.56cm)
Mini DisplayPort	1x miniDisplayPort port (v.1.2 spec compliant, up to 3840x2160@30Hz)	Master Carton	
VGA	1x VGA port (up to 1920x1200@60Hz)	Width	14.25" (36.2cm)
Ethernet	1x Gigabit Ethernet port	Height	5.25" (13.34cm)
USB-A	3x USB 3.0 A ports, 1 port with BC1.2 charging	Depth	9" (22.86cm)
USB-C	1x USB-C port (charging only)	Master Carton Qty.	6
Card Reader	Supports SD/SDHC/SDXC @ UHS-I class, MMC	Weight	
Power		Master Carton Wt.	6.68 lb (3.03kg)
Power Delivery Pass-Thru	PD Pass-Thru up to 60W	Unit Pack Wt.	0.92 lb (0.45kg)
Operating System Requirements		Unit Wt.	0.70 lb (0.32kg)
Windows	Windows 7 / 8 / 8.1 / 10		
Mac	Mac OS X 10.10.5+		