



## Square Insert & Power Bits

### Square Bits







CVM, tool steel, hardened

 Square

Suitable for all applications for both manual & machine hardness HRC 59-61







#### 718 Square Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
71801	1	25	10	.11
71802	2	25	10	.11
71803	3	25	10	.11

#### 30 Piece Contractor Grade Bits

#### 725 Square Insert Contractor Grade, 1/4"


Item				
No.	mm	mm	pkg.	lbs.
72537	1	25	30 pc	.85
72538	2	25	30 pc	.85
72539	3	25	30 pc	.85

2 bit pack



#### 718 Square Insert Bit Packs, 1"


CVM S2 modified tool steel.

Item				
No.	Size	mm	lbs.	
71851	1	25	.03	
71852	2	25	.03	
71853	3	25	.03	

#### 71854 Square Insert Bit Packs, 1"

CVM S2 modified tool steel. 3 pc. bit pack



71854 Set includes the following bits:

 Square: wt. .04 1, 2, 3 x 1" (25mm)

2 bit pack







#### 777 Square Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item		
No.	Size	mm
77712	#1 + #2	30
77713	#0 + #3	30



#### 748 Square Power Bits. 1/4" Hex Drive, Length 2.0"/50mm




Item				
No.	Size	mm	pkg.	lbs.
74813	1	50	10	.20
74816	2	50	10	.20
74819	3	50	10	.20


2 bit pack



#### 748 Square Power Bit Packs, 2"

CVM S2 modified tool steel.


Item			
No.	Size	mm	lbs.
74860	1	50	.05
74861	2	50	.05
74862	3	50	.05



#### 74890 Square Power Bit Packs, 2" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

74890 Set includes the following bits:


 Square: wt. .08 1, 2, 3 x 2.0" (50mm)



#### 74895 Square Power Bit Packs, 2.0" CVM




S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

74895 Set includes the following bits:

 Square: 2 of each sizes wt. 1.2 1, 2, 3 x 2.0" (50mm)



#### 748 Square Power Bit, 1/4" Hex Drive, Length 3.5"/90mm CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
74811	1	90	.08
74812	2	90	.08
74814	3	90	.08

## Slotted Bits

The ideal multi-purpose bits for all around quality & performance

Made by Wiha - Production Quality








Highly resistant to wear and tear for a long tool life

 Slotted

Impact resistant modified CVM, tool steel, hardened







#### 710 Slotted Insert Bits, 1/4" Hex Drive, Length 25mm/.984"

Item					
No.	mm	Inch	mm	Inch	pkg.
71001	4.5	.177	0.6	.024	10
71004	5.5	.216	0.8	.030	10
71002	6.5	.255	1.2	.039	10
71003	8.0	.315	1.6	.063	10

#### 30 Piece Contractor Grade Bits






#### 725 Slotted Insert Contractor Grade, 1/4"

Item				
No.	mm	mm	pkg.	lbs.
72534	4.5	25	30 pc	.85
72535	5.5	25	30 pc	.85
72536	6.0	25	30 pc	.85

2 pc. bit pack!





#### 710 Slotted Insert Bits. 1/4" Hex Drive, Length 1.54"/39mm 2 pc. Bit pack.

Item					
No.	mm	Inch	mm	Inch	pkg.
71030	3.0	.118	0.5	.020	2
71031	3.5	.139	0.6	.024	2
71032	4.0	.157	0.8	.031	2
71033	4.5	.177	0.6	.024	2
71034	5.5	.216	1.0	.039	2
71035	6.5	.255	1.2	.047	2
71036	8.0	.315	1.6	.063	2

2 bit pack



#### 777 Slotted Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item		
No.	Size	mm
77715	3.0 + 4.5mm	30
77716	4.0 + 6.0mm	30
77717	5.5 + 6.5mm	30