


**ModuPlug
HDC XX5E01 FMSRJ45-0100**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Type	HDC XX5E01 FMSRJ45-0100
Order No.	2451080100
Version	
GTIN (EAN)	4050118467994
Qty.	1 pc(s).

**ModuPlug
HDC XX5E01 FMSRJ45-0100**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.001 g
------------	---------

Temperatures

Limit temperature	-30 °C ... 90 °C
-------------------	------------------

General data

Module side version	Female	Opposite side version	Male, straight, RJ45
Cable length	1 m	Category	Cat. 5e
Coding	D	Contact surface	Au (Gold)
Insulation resistance	$\geq 10^8 \Omega$	No. of poles	4
Plugging cycles	≥ 100	Pollution severity	2
Rated current	4 A	Rated voltage	250 V
Transmission rate	100 Mbit/s		

Cable technical specifications

Cable length	1 m	Colour coding	white, yellow, blue, orange
Core cross-section	22 AWG	Halogen	No
Insulation	PE	Outside diameter	6.5 ± 0.2
Sheath material	PUR	Sheathing colour	Green
Shielded	Yes		

Classifications

ETIM 6.0	EC000438	eClass 6.2	27-26-12-04
eClass 9.1	27-44-02-18		

Product information

Descriptive text technical data	Round plug-in connector in accordance with IEC 61076-2-101
---------------------------------	--

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN
--------------------	------------------------------------

Data sheet**ModuPlug
HDC XX5E01 FMSRJ45-0100**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

RJ45		M12
1	yellow	1
3	white	2
2	orange	3
6	blue	4
