

Wiha Phillips Insert Bits



711 Phillips Insert Bits, 1/4"

Item	+	—	↵
No.	Size	mm	pkg. lbs.
71100	0	25	10 .10
71101	1	25	10 .11
71102	2	25	10 .11
71103	3	25	10 .11

711 Phillips Insert Bit Bulk Packs, 1/4"

No.	Size	mm	pkg.	lbs.
71125	2	25	25 pc	.30
71150	2	25	50 pc	.62
71199	2	25	100 pc	1.20

725 Phillips Insert Contractor Grade, 1/4"

No.	Size	mm	pkg.	lbs.
72519	0	25	30 pc	.85
72521	1	25	30 pc	.85
72522	2	25	30 pc	.85
72523	3	25	30 pc	.85

Phillips Bits

The ideal multi-purpose bits for all around quality & performance

Made by Wiha - Production Quality

Suitable for all applications for both manual and machine
Hardness HRC 59-61



Impact resistant modified CVM, tool steel, hardened

Highly resistant to wear and tear for a long tool life



Phillips

High grade CVM steel, hardened torsion zone to prevent uneven torque distribution DIN 3126 ISO 1173 with anti-camout ribs

Wiha Phillips Insert Bit Packs

2 bit pack



711 Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel

Item	+	—	↵
No.	Size	mm	lbs.
71149	0	25	.03
71151	1	25	.03
71152	2	25	.03
71153	3	25	.04



71155 Phillips Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71155 Set includes the following bits:

↵ + Phillips:
wt. .08 6 pieces 2 x 1" (25mm)

2 bit pack



777 Phillips Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

S2 modified tool steel

Item	+	—
No.	Size	mm
77707	#1 + #2	30
77708	#0 + #3	30



71154 Phillips Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

71154 Set includes the following bits:

↵ + Phillips:
wt. .04 1, 2, 3 x 1" (25mm)




71056 Slotted/Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel. Extra hard with natural finish, exact fit machined tips. 6 pc. bit pk.

71056 Set includes the following bits:

⊖ Slotted:
4.5, 5.5, 6.5 x 1" (25mm)

+ Phillips:
1, 2, 3 x 1" (25mm) .08



10 bit pack



71132 Phillips Drywall Stop Bit

High grade Chrome-vanadium steel, through hardened. Ideal bit for drywall constructors. Blue ring prevents the screw from being recessed too deeply into the plasterboard.

Item	+	—	↵	⊖
No.	Size	mm	lbs.	Pkg.
71132	2	25	.20	10

