# **HPH J-Hooks**

The High Performance Hybrid J-Hooks are 2" wide, designed with a reusable Snap-Lock latch for securing cable, and are UL listed and Plenum rated.

#### **Features**

- Wide base support 2"
- Industry leading bend radius
- Snap-Lock latch firmly secures cables
- Eliminates the use of Cable Ties/Velcro Ties
- Made with easy slide, slick, burr free surface
- No pressure points
- Light-weight
- Flush mount for easy installation
- Economical

### **Technical**

- cULus Listed
- Plenum Rated
- RoHS Compliant
- TIA Compliant

## **Sizing**

The HPH J-Hooks come in four sizes and are available assembled to the most common fasteners:

- HPH16 (1")
- HPH32 (2")
- HPH48 (3")
- HPH64 (4")

See reverse side for part numbers, ordering information, cable capacities, and special order custom assemblies



99 Washington Street Melrose, MA 02176 Phone 781-665-1400 Toll Free 1-800-517-8431









## **How to Order:**







	Cable Capacity					
	Cat5e	Cat6	Cat6A	Standard HPH	90° HPH	Batwing HPH
1"				P/N <b>HPH16-25</b>	P/N <b>HPH16AC-25</b>	P/N <b>HPH16W-25</b>
Size 16	20	15	10	25/Box	25/Box	25/Box
2"				P/N <b>HPH32-25</b>	P/N <b>HPH32AC-25</b>	P/N <b>HPH32W-25</b>
Size 32	90	60	35	25/Box	25/Box	25/Box
3"				P/N <b>HPH48-25</b>	P/N <b>HPH48AC-25</b>	P/N <b>HPH48W-25</b>
Size 48	200	150	80	25/Box	25/Box	25/Box
4"				P/N <b>HPH64-25</b>	P/N <b>HPH64AC-25</b>	P/N <b>HPH64W-25</b>
Size 64	330	220	140	25/Box	25/Box	25/Box

Note: Cable Capacity refers to the number of cables per J-Hook

# **Special Order Information**

"XX" stands for the size of the HPH J-Hook. Sizes range from 1"(16), 2"(32), 3"(48), and 4"(64). Part numbers are for special order purposes only. For more information, please contact Platinum Tools.

Example: HPH32BC-25

HPH J-Hook, size 32 (2"), Steel Beam Clamp, Swivels 360°



HPHXXBC-25 Steel Beam Clamp, swivels 360°



HPHXXPA-25 Right Angle Powder Actuated



HPHXXACSSBC-25 Spring Steel Beam Clamp, swivels 360°



HPHXXSSBCF-25 Spring Steel Beam Clamp Fixed



HPHXXVO-25 Vertical Overhang for "C" Purlin



HPHXXACFM58-25 Hammer-On Beam Clamp, swivels 360°



HPHXXAO-25 Angled Overhang for "Z" Purlin



HPHXXBCF-25 Steel Beam Clamp Fixed



HPHXXHOK58-25 Hammer-On Beam Clamp, fixed

Test Equipment
Depot
1-800-517-8431

99 Washington Street Melrose, MA 02176 Phone 781-665-1400 Toll Free 1-800-517-8431