

Find A Retailer

Product Registration



Search



## PCCK600LB 20V MAX\* 1/2 IN. CORDLESS DRILL/DRIVER KIT



3.5 (2)

[Write a review](#)

This 20V MAX\* 1/2 in. Lithium Ion Drill/Driver Kit lets you power through the toughest metal drilling, wood drilling, and fastening jobs. With a compact and lightweight design, this Drill/Driver is designed to eliminate user fatigue, but it doesn't compromise on speed and power thanks to its two-speed gearbox and high-output motor. Packed with two PCC680L batteries and a PCC690L charger, this is the kit you need whether you're installing cabinetry, framing out rooms, or fastening hinges on doors.

[READ LESS](#) ▲

[BUY NOW](#)

**SHARE THIS PRODUCT:**

**IMPORTANT LINKS**

[FEATURES & SPECS](#)

[WARRANTY](#)

[USER REVIEWS](#)

# FEATURES & SPECS

## FEATURES

- High performance motor delivers 330 Unit Watts Out
- 2 Speed gear box (0-400/0-1,600) delivers the power needed to complete large and small applications
- Metal ratcheting chuck minimizes bits slipping in chuck
- Battery gauge displays charge remaining in the battery
- LED light brightens dark work areas
- Compact size (7 3/4" length) and light weight (3.5lbs) allows tool to work in tight areas and minimizes user fatigue
- 20V Max Lithium Ion batteries with 1.5 amp/hour cells delivers more power and runtime in a smaller package

## SPECIFICATIONS

<b>BATTERY TYPE</b>	LITHIUM ION
<b>CHUCK SIZE</b>	1/2"
<b>CHUCK TYPE</b>	KEYLESS
<b>CLUTCH SETTINGS</b>	23
<b>KIT BOX</b>	NONE
<b>MAX POWER</b>	330 UWO
<b>NO LOAD SPEED</b>	0-1600 RPM
<b># OF SPEED SETTINGS</b>	2
<b>POWER TOOL TYPE</b>	CORDLESS
<b>TOOL LENGTH</b>	7.75 IN
<b>UNITS WATTS OUT</b>	330

## INCLUDES

- (1) PCC600 Drill/Driver
- (2) PCC680L Lithium Ion Compact Batteries

- (1) PCC690L Lithium Ion Charger
- Double-Ended Bit Tip
- Kit Box

# WARRANTY & SERVICE INFORMATION

## WARRANTY INFORMATION

<b>3</b>	3 YEAR LIMITED WARRANTY (TOOL ONLY) GARANTIE LIMITÉE DE 3 ANS (OUTIL SEULEMENT) 3 AÑOS DE GARANTÍA LIMITADA (SOLO HERRAMIENTA)
<b>1</b>	1 YEAR FREE SERVICE SERVICE GRATUIT PENDANT 1 AN 1 AÑO DE SERVICIO GRATUITO
<b>90</b>	90 DAY MONEY BACK GUARANTEE GARANTIE DE REMBOURSEMENT DE 90 JOURS GARANTÍA DE REEMBOLSO DE 90 DÍAS

## MANUALS

[INSTRUCTION MANUAL](#) ▶▶

[LOOKING FOR SERVICE?](#)

★★★★★ 3.5 | 2 Reviews

1 out of 2 (50%) reviewers recommend this product



## Reviews

[Write a review](#)

Rating Snapshot

Average Customer Ratings

Select a row below to filter reviews.

Overall



3.5