


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0310671070](#)
Status: **Active**
Overview: H-DAC 64 Unsealed Connector System
Description: 2.54mm H-DAC 64, 3 Way Male Housing Assembly, Single Row, Polarization A, with Xmas Tree Attachment, Black

Documents:

3D Model	Packaging Specification PK-30907-737 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-076 (PDF)
Product Specification PS-31067-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-31067-100-001 (PDF)	



General

Product Family	Crimp Housings
Series	31067
Application	Power, Wire-to-Board
Comments	Polarization Option A, Black
Overview	H-DAC 64 Unsealed Connector System
Product Name	H-DAC 64
UPC	800756062662

Physical

Circuits (maximum)	3
Circuits Detail	3
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	2.044/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +100°C

Electrical

Current - Maximum per Contact	11.0A, 9.0A
-------------------------------	-------------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-31067-100-001
Packaging Specification	PK-30907-737, PK-31301-076
Product Specification	PS-31067-0001-001
Sales Drawing	SD-31110-003

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[31067 Series](#)

Mates With

H-DAC 64 3 Way Receptacle Assembly
[31067-1010](#)

Use With

See Product Specification

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION