





DECOSTAR® 51 ALU

DECOSTAR® 51 STANDARD, DECOSTAR® 51S STANDARD



Product reference

Product number



*

DECOSTAR® 51 ALU solves the problem of heat build-up.

DECOSTAR® 51 ALU, with aluminium coated reflector and low pressure design

Product reference	Product number	W	V	Beam angle	cd	GU5.3	d [mm]	l max. [mm]	t [h]	Packaging
41861WFL	4050300428819	20	12	38	700	GU5.3	51	45	3000	20
41866WFL	4050300428833	35	12	38	1100	GU5.3	51	45	3000	20
41871WFL	4050300428857	50	12	38	1800	GU5.3	51	45	3000	20

DECOSTAR® ALU

The aluminium-coated reflector without a shield reduces the thermal load in the luminaire by about 80% compared with dichroic reflectors with a shield.

The dimmable lamp with UV-reducing quartz (as per IEC 60432) offers a consistent light throughout the life of the lamp.

DECOSTAR® ALU and STANDARD can be operated in open luminaires (as per IEC 60598).

Product reference

Product number



*

DECOSTAR® 51 STANDARD, 51 mm dia., without shield




Product reference	Product number	W	V	Beam angle	cd	GU5.3	d [mm]	l max. [mm]	t [h]	No.	Packaging
41860SP ¹⁾	4050300012612	20	12	10	3150	GU5.3	51	45	2000	1	20
41860WFL ¹⁾	4050300012629	20	12	38	510	GU5.3	51	45	2000	1	20
41865SP ¹⁾	4050300026527	35	12	10	6300	GU5.3	51	45	2000	1	20
41865WFL ¹⁾	4050300026541	35	12	38	1050	GU5.3	51	45	2000	1	20
41870SP ¹⁾	4050300012636	50	12	10	8200	GU5.3	51	45	2000	1	20
41870WFL ¹⁾	4050300012575	50	12	38	1500	GU5.3	51	45	2000	1	20

DECOSTAR® 51S STANDARD, 51 mm dia., with shield

Product reference	Product number	W	V	Beam angle	cd	GU5.3	d [mm]	l max. [mm]	t [h]	No.	Packaging
44860SP	4050300272474	20	12	10	3000	GU5.3	51	45	2000	2	20
44860WFL	4050300272511	20	12	38	480	GU5.3	51	45	2000	2	20
44865SP	4050300272559	35	12	10	6000	GU5.3	51	45	2000	2	20
44865WFL	4050300272634	35	12	38	1000	GU5.3	51	45	2000	2	20
44870SP	4050300272672	50	12	10	7800	GU5.3	51	45	2000	2	20
44870WFL	4050300272795	50	12	38	1450	GU5.3	51	45	2000	2	20

OSRAM DECOSTAR® with its clear DECO cover protects the reflector coating against dust, moisture and contact. The brilliance and mother-of-pearl effect of the reflector remain unaffected.

- Complies with the strictest UV protection thresholds (erythema, NIOSH).
- DECOSTAR® lamps are dimmable.
- Flat clear shield so the lamps can be used in open luminaires to IEC 60598.



¹⁾ Discontinued
* To ensure that your order reaches you quickly, please order standard pack quantities