



*Quality Products. Service Excellence.*

## ABS Plastic Tablet Enclosures *1599TAB Series*

Ergonomic Design, PC Board Standoffs, Battery Compartments

### Features



- Low profile - ergonomically designed for a comfortable fit into the user's hands.
- Perfect for instrument or mobile data enclosures requiring a touch screen.
- Choice of three size. All available with or without battery compartment.
- Molded from flame retardant ABS plastic, choice of black or grey - material carries a UL flammability rating of 94V-0.
- Enclosure is assembled with six (6) - M3-0.5 x 18 mm Phillips machine screws, threaded into integral brass bushings. Perfect for applications when repetitive assembly and disassembly are required.
- Integral brass bushings are factory inserted into the top half of the enclosure (see photos).
- Lap joint construction provides protection against access of dust and splashing water. Designed to meet IP54.
- P.C. board standoffs are molded into case top & bottom halves (see drawings or photos for more details).
- Battery door & compartment version (part numbers ending in "BAT") includes 8 battery clips (for 4 - AA batteries) and two 9 volt (PP3) battery clips.
- Contains one end panel - removable for easy modification.
- Bottom half of enclosure includes a square - molded inlay for labels.

### Screws

100 pack of silver replacement cover screws (M3-0.5 x 18mm Flat Head), part number **1594MS100**

100 pack of black replacement cover screws (M3-0.5 x 18mm Flat Head), part number **1594MS100BK**

50 pack of optional PC board screws (#4 x 1/4" Self Tapping), part number **1593ATS50**

100 pack of optional PC board screws (#4 x 1/4" Self Tapping), part number **1593ATS100**

### Photo Features



Battery compartment options include clips for AA's and 9V batteries.



Available in three sizes, two colors (black and grey) and with or without battery compartments.

### Tablet Enclosures

Part Number	Color	Battery Door & Compartment	Removable End Panel	Length	Width	Depth
1599TABSBK	Black	No	Yes	4.72	3.74	1.06
1599TABSGY	Grey	No	Yes	4.72	3.74	1.06
1599TABSBKBAT	Black	Yes	Yes	4.72	3.74	1.06
1599TABSGYBAT	Grey	Yes	Yes	4.72	3.74	1.06
1599TABMBK	Black	No	Yes	6.67	5.31	1.06
1599TABMGY	Grey	No	Yes	6.67	5.31	1.06
1599TABMBKBAT	Black	Yes	Yes	6.67	5.31	1.06
1599TABMGYBAT	Grey	Yes	Yes	6.67	5.31	1.06
1599TABLBK	Black	No	Yes	9.45	7.48	1.18
1599TABLGY	Grey	No	Yes	9.45	7.48	1.18
1599TABLBKBAT	Black	Yes	Yes	9.45	7.48	1.18
1599TABLGYBAT	Grey	Yes	Yes	9.45	7.48	1.18

Tags: 1599, tablet

Data subject to change without notice

© 2019. Hammond Manufacturing Ltd. All rights reserved.