

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **1600744001**  
**Status:** **Active**  
**Overview:** MX150 Sealed and Unsealed Connector System  
**Description:** MX150 Mat-Sealed Female Connector Assembly, Dual Row, 8 Circuits, UL 94V-0, Keying Option A, without Connector Position Assurance, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31300-635-001 (PDF)</a>
<a href="#">Product Specification PS-160074-0001-001 (PDF)</a>	<a href="#">Packaging Specification PK-31300-903-001 (PDF)</a>
<a href="#">Application Specification AS-33472-100-001 (PDF)</a>	<a href="#">Test Summary 1600742276-TS-000 (PDF)</a>
<a href="#">Application Specification AS-33472-100-CH-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-33472-100-FR-001 (PDF)</a>	

**Agency Certification**

UL E29179

**General**

Product Family	Crimp Housings
Series	<u>160074</u>
Application	Power, Wire-to-Board, Wire-to-Wire
More Detailed Tech Information	<a href="http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership">http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership</a>
Overview	<u>MX150 Sealed and Unsealed Connector System</u>
Polarization	A
Product Name	MX150
UPC	889056421379

**Physical**

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	13.828/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33472-100-FR-001
Packaging Specification	PK-31300-635-001, PK-31300-903-001
Product Specification	PS-160074-0001-001
Sales Drawing	SD-160074-0002-001, SD-33472-0001-001
Test Summary	1600742276-TS-000



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/71/2019 (16 July 2019)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Compliant

Not Contained

**Search Parts in this Series**

160074 Series

**Mates With**

160084 Male Dual Row Sealed Connector

**Use With**

MX150 Female Terminal 33012 , 33001  
<br>MX150 Sealed Receptacle Cavity Plug 343454001

This document was generated on 11/20/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**