


Replacement die - CF 500/DIE SC 6 - 1212242


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die for crimping machine CF 500, for slip-on sleeves and flat connectors (C-SCF... and C-SCM...) 0.5 ... 6 mm²



Key Commercial Data

| | |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit | 1 pc |
| GTIN |  4 046356 450003 |
| GTIN | 4046356450003 |
| Weight per Piece (excluding packing) | 73.000 g |
| Custom tariff number | 84799070 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|----------------|-------------------|
| Cable diameter | 0.9 mm ... 2.9 mm |
|----------------|-------------------|

General

| | |
|--------------------|---------------------|
| Compression | B crimp |
| Min. cross section | 0.5 mm ² |
| Max. cross section | 6 mm ² |
| Min. cross section | 0.5 mm ² |
| Max. cross section | 6 mm ² |

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 17139201 |
| eCl@ss 4.0 | 21043000 |
| eCl@ss 4.1 | 21043000 |

Replacement die - CF 500/DIE SC 6 - 1212242

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.0 | 21059000 |
| eCl@ss 5.1 | 21059000 |
| eCl@ss 6.0 | 21049000 |
| eCl@ss 7.0 | 21049090 |
| eCl@ss 8.0 | 21049090 |
| eCl@ss 9.0 | 17139201 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC001282 |
| ETIM 5.0 | EC001282 |
| ETIM 6.0 | EC001282 |
| ETIM 7.0 | EC001282 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 27111518 |
| UNSPSC 13.2 | 27111518 |
| UNSPSC 18.0 | 27111518 |
| UNSPSC 19.0 | 27111518 |
| UNSPSC 20.0 | 27111518 |
| UNSPSC 21.0 | 27111518 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|--|--------------------------|
| EAC | | RU C- DE.AI30.B.01549 |
|-----|--|--------------------------|

Replacement die - CF 500/DIE SC 6 - 1212242

Accessories

Accessories

Cover

Covering hood - CF 500/COV SC - 1212251



Protective cover for crimping machine CF 500, for flat sleeve connector and flat connector 0.1-6 mm², SC 1.5... and SC 6...

Sleeve receiver

Spare locator - CF 500/LOC SCF 4,8/2,5 - 1212248



Sleeve receiver for CF 500 crimping machine, for slip-on sleeves (SCF 4,8...), 0.5 - 2.5 mm², width: 4.8 mm

Spare locator - CF 500/LOC SCF 6,3/6 - 1212247



Sleeve receiver for CF 500 crimping machine, for slip-on sleeves (SCF 6,3...), 0.5 - 6 mm², width: 6.3 mm

Spare locator - CF 500/LOC SCM 6,3/2,5 - 1212264



Sleeve receiver for CF 500 crimping machine, for (SCM...) 0.5 - 2.5 mm flat plug, width: 6.3 mm

Spare locator - CF 500/LOC SCM 6,3/6 - 1212265



Sleeve receiver for CF 500 crimping machine, for (SCM...) 1.5 - 6 mm flat plug, width: 6.3 mm
