

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1510492206](#)
Status: **Active**
Overview: CP Wire-to-Board and Wire-to-Wire Connector Systems
Description: CP-6.5 Receptacle Housing, 6.50mm Pitch, Dual Row, Polarized, Positive Lock, 2 Circuits, Black

Documents:

3D Model	Packaging Specification PK-151049-0001-001 (PDF)
Drawing (PDF)	Test Summary 1510480001-TS-000 (PDF)
Product Specification PS-151048-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	151049
Application	Power, Wire-to-Board
Comments	See Product Specification for maximum current rating by circuit size and wire AWG, See Product Specification for maximum current rating by circuit size and wire AWG
Overview	CP Wire-to-Board and Wire-to-Wire Connector Systems
Product Name	CP-6.5
UPC	889056065719

Physical

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBTP
Net Weight	1.007/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.50mm
Pitch - Termination Interface	6.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-151049-0001-001
Product Specification	PS-151048-0001-001
Sales Drawing	SD-151049-0001-001
Test Summary	1510480001-TS-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[151049](#) Series

Mates With

CP-6.5 Headers [1510481206](#) , [1510482206](#)

Use With

Female Crimp Terminal 16-22 AWG Wire [505978000](#) , Female Crimp Terminal 20-26 AWG Wire [505988000](#) , Crimp Terminal Retainer [511430105](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION