

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194360411](#)
Status: **Active**
Overview: [MX150L Industrial Sealed Connector System](#)
Description: MX150L 4 Circuit Rear Mount Flange Sealed Panel Mount Plug for 10-12 AWG Wire, with Gasket, Black

Documents:

3D Model	Packaging Specification PK-19436-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19432-001-001 (PDF)	Product Literature (PDF)

General

Product Family	Crimp Housings
Series	19436
Application	Power, Wire-to-Wire
Comments	Mat Seal Color Yellow, Polarized to Mating Part. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec, Mat Seal Color Yellow, Polarized to Mating Part. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec
Overview	MX150L Industrial Sealed Connector System
Product Literature Order No	987650-2181
Product Name	MX150L
UPC	800756731889

Physical

Circuits (maximum)	4
Circuits Detail	2x2
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	7.62mm
Pitch - Termination Interface	7.62mm
Polarized to Mating Part	No
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +125°C


Electrical

Current - Maximum per Contact	40.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19436-001
Product Specification	PS-19432-001-001
Sales Drawing	SD-19436-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19436](#) Series

Mates With

[19432](#) Receptacle

Use With

This document was generated on 03/28/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION