

Connector - C-SCF 1,5/6,3X0,8 - 3240156

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Slip-on sleeve, non-insulated, 0.5 ... 1.5 mm², 6.3 x 0.8

Your advantages

- The uninsulated slip-on sleeves and flat plugs are made from electrolytically tin-plated brass
- They round out the product range in terms of connectors

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| GTIN |  4 046356 453738 |
| GTIN | 4046356453738 |
| Weight per Piece (excluding packing) | 0.820 g |
| Custom tariff number | 85369010 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--------------------------|---------|
| Length (b) | 19.2 mm |
| Width (a) | 6.3 mm |
| Maximum stripping length | 7 mm |
| Material thickness (g) | 0.4 mm |

Ambient conditions

| | |
|---------------------------------|--------|
| Ambient temperature (operation) | 110 °C |
|---------------------------------|--------|

General

| | |
|------------------|--------|
| Color | silver |
| Stripping length | 7 mm |

Connector - C-SCF 1,5/6,3X0,8 - 3240156

Technical data

General


| | |
|---------------------|------------------|
| Components | halogen-free |
| Material | Brass |
| Insulating material | nicht zutreffend |
| Coating | tin-plated |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Drawings

Dimensional drawing



Connector - C-SCF 1,5/6,3X0,8 - 3240156

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060700 |
| eCl@ss 4.1 | 27060700 |
| eCl@ss 5.0 | 27400200 |
| eCl@ss 5.1 | 27400200 |
| eCl@ss 6.0 | 27400200 |
| eCl@ss 7.0 | 27400204 |
| eCl@ss 8.0 | 27400204 |
| eCl@ss 9.0 | 27400212 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC001052 |
| ETIM 5.0 | EC000516 |
| ETIM 6.0 | EC001059 |
| ETIM 7.0 | EC001059 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211923 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121707 |
| UNSPSC 19.0 | 27121707 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|--|---------------|
| EAC | | EAC-Zulassung |
|-----|--|---------------|

Connector - C-SCF 1,5/6,3X0,8 - 3240156

Accessories

Accessories

Crimping tool

Crimping pliers - CRIMPFOX-SC 6 - 1212050



Crimping pliers, for uninsulated slip-on sleeves 2.8, 4.8, and 6.3 mm, 0.5 - 6 mm², B crimp


Die

Replacement die - CF 500/DIE SC 1,5 - 1212241



Die for crimping machine CF 500, for slip-on sleeves and flat connectors (C-SCF... and C-SCM...) 0.1 ... 1.5 mm²

Replacement die - CF 500/DIE SC 6 - 1212242



Die for crimping machine CF 500, for slip-on sleeves and flat connectors (C-SCF... and C-SCM...) 0.5 ... 6 mm²

Replacement die - CF 500/DIE SC 1,5 - 1212241



Die for crimping machine CF 500, for slip-on sleeves and flat connectors (C-SCF... and C-SCM...) 0.1 ... 1.5 mm²

Replacement die - CF 500/DIE SC 6 - 1212242



Die for crimping machine CF 500, for slip-on sleeves and flat connectors (C-SCF... and C-SCM...) 0.5 ... 6 mm²
